



Sample photo

Order symbol: AR865CHL
Product nbr: 8561022
Description: PC Enclosure
Remarks: Hinged opaque cover w/Plastic quick release latch

EAN: 6418074066893
El. number:
Finland:
:
Norway:

Including: Hinged cover base with 10-32 brass inserts, latched cover with formed in place PUR gasket, and stainless hinge pin. Quick release latches. (Latch options available.) Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Dimensions:				Rating:
Length	Width	Height		
mm: 203	152	127		Ingress Protection (EN 60529): IP 66/67
inch: 8.0	6.0	5.0		Impact Resistance (EN 62262): IK 08/07
Materials:				Electrical insulation: Totally insulated
Material:	Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:	RAL 7035			UV resistance: UL 508
Cover colour:	RAL 7035			Flammability Rating (UL 746 C 5): complies with UL 508
Cover screws material:	Stainless steel			Glow Wire Test (IEC 695-2-1) °C: 960
Gasket material:	Polyurethane			NEMA Class: NEMA 4, 4X, 6, 6P, 12, 13
Temperatures:				Certificates:
Short term:	-40 ... 140 °C			Underwriters Laboratories
Continuous:	-40 ... 80 °C			Europe EN 62208: 2003
Short term:	-40 ... 284 °F			
Continuous:	-40 ... 175 °F			
Accessories:				
ABP86	Painted Steel Back Panel			
ALBP86	Aluminum Back Panel			
ADFP86	Dead Front Panel w/ screws			
ASP86	Aluminum Swing Panel			
ASPK86	Swing Panel Kit incl. Panel			
ASPHK8	Swing Panel Kit w/o Panel			
AMFL6	6" Mounting Flange Set			

