

Connector/Cable Cross Reference Guide

	Cable Part#	F		BNC		RCA	
		SNAP-N-SEAL	DOUBLE-BUBBLE	SNAP-N-SEAL	DOUBLE-BUBBLE	SNAP-N-SEAL	DOUBLE-BUBBLE
		 CPLCCT-SLM	 CPLCRBC-BR	 CPLCCT-SLM	 CPLCRBC-BR	 CPLCCT-SLM	 CPLCRBC-BR
25-26 AWG Center Conductor: .015 ~ .025 Dielectric: .065 ~ .078 Outer Jacket: .095 ~ .110	1277P	-	-	FS1BNC	DB1BNC DB1BNCHD	FS1RCA	DB1RCA
	1277R	-	-	FS1BNC	DB1BNC DB1BNCHD	FS1RCA	DB1RCA
	1278R	-	-	FS1BNC	DB1BNC DB1BNCHD	FS1RCA	DB1RCA
	1279P	-	-	FS1BNC	DB1BNC DB1BNCHD	FS1RCA	DB1RCA
	1279R	-	-	FS1BNC	DB1BNC DB1BNCHD	FS1RCA	DB1RCA
	1280P	-	-	FS1BNC	DB1BNC DB1BNCHD	FS1RCA	DB1RCA
	1280R	-	-	FS1BNC	DB1BNC DB1BNCHD	FS1RCA	DB1RCA
	1281R	-	-	FS1BNC	DB1BNC DB1BNCHD	FS1RCA	DB1RCA
	1394P	-	-	FS1BNC	DB1BNC DB1BNCHD	FS1RCA	DB1RCA
	1395R	-	-	FS1BNC	DB1BNC DB1BNCHD	FS1RCA	DB1RCA
	1395P	-	-	FS1BNC	DB1BNC DB1BNCHD	FS1RCA	DB1RCA
	1396R	-	-	FS1BNC	DB1BNC DB1BNCHD	FS1RCA	DB1RCA
	1396P	-	-	FS1BNC	DB1BNC DB1BNCHD	FS1RCA	DB1RCA
	1281S3	-	-	FS1BNC	DB1BNC DB1BNCHD	FS1RCA	DB1RCA
	1281S5	-	-	FS1BNC	DB1BNC DB1BNCHD	FS1RCA	DB1RCA
	1281S6	-	-	FS1BNC	DB1BNC DB1BNCHD	FS1RCA	DB1RCA
	1282S3	-	-	FS1BNC	DB1BNC DB1BNCHD	FS1RCA	DB1RCA
	1282S5	-	-	FS1BNC	DB1BNC DB1BNCHD	FS1RCA	DB1RCA
	1282S6	-	-	FS1BNC	DB1BNC DB1BNCHD	FS1RCA	DB1RCA
	1283S3	-	-	FS1BNC	DB1BNC DB1BNCHD	FS1RCA	DB1RCA
	1283S5	-	-	FS1BNC	DB1BNC DB1BNCHD	FS1RCA	DB1RCA
22-24 AWG Center Conductor: .015 ~ .025 Dielectric: .095 ~ .105 Outer Jacket: .145 ~ .160	1164B	FS15	-	FS15BNC	DB15BNCHD	FS15RCA	DB15RCA
	1371P	FS15	-	FS15BNC	DB15BNCHD	FS15RCA	DB15RCA
	1371R	FS15	-	FS15BNC	DB15BNCHD	FS15RCA	DB15RCA
	1406B	FS15	-	FS15BNC	DB15BNCHD	FS15RCA	DB15RCA
	1407B	FS15	-	FS15BNC	DB15BNCHD	FS15RCA	DB15RCA
	1417B	FS15	-	FS15BNC	DB15BNCHD	FS15RCA	DB15RCA
	1418B	FS15	-	FS15BNC	DB15BNCHD	FS15RCA	DB15RCA
	1855A	FS15	-	FS15BNC	1855ABHD1 1855ABHDL	FS15RCA	DB15RCA
	7787A	FS15	-	FS15BNC	DB15BNCHD	FS15RCA	DB15RCA
	7788A	FS15	-	FS15BNC	DB15BNCHD	FS15RCA	DB15RCA
	7789A	FS15	-	FS15BNC	DB15BNCHD	FS15RCA	DB15RCA
	7790A	FS15	-	FS15BNC	DB15BNCHD	FS15RCA	DB15RCA
	7791A	FS15	-	FS15BNC	DB15BNCHD	FS15RCA	DB15RCA
	7792A	FS15	-	FS15BNC	DB15BNCHD	FS15RCA	DB15RCA
	7796A	FS15	-	FS15BNC	DB15BNCHD	FS15RCA	DB15RCA
	8218	FS15	-	FS15BNC	DB15BNCHD	FS15RCA	DB15RCA
	1855S3	FS15	-	FS15BNC	DB15BNCHD	FS15RCA	DB15RCA
	1855S5	FS15	-	FS15BNC	DB15BNCHD	FS15RCA	DB15RCA
	57394S	FS15	-	FS15BNC	DB15BNCHD	FS15RCA	DB15RCA
	67394B	FS15	-	FS15BNC	DB15BNCHD	FS15RCA	DB15RCA

Connector/Cable Cross Reference Guide

Cable Part#	F		BNC		RCA	
	SNAP-N-SEAL	DOUBLE-BUBBLE	SNAP-N-SEAL	DOUBLE-BUBBLE	SNAP-N-SEAL	DOUBLE-BUBBLE
						
	CPLCCT-SLM	CPLCRBC-BR	CPLCCT-SLM	CPLCRBC-BR	CPLCCT-SLM	CPLCRBC-BR
RG59 Center Conductor: .0317 ~ .0399 Dielectric: .144 ~ .157 Outer Jacket: .232 ~ .273	1186A	FSNS59U SNS1P59U DB59U	FSNS59BNCU	DB59BNCU	FSNS59RCAU	DB59RCAU
	1370R	FS59PL2 DB59PL2/5	FS59BNCPL2	DB59BNCPL2/4	FS59RCAPL2	DB59RCAPL2/4
	1426A	FSNS59U SNS1P59U DB59U	FS59BNC SL	DB59BNC SL	FS59RCASL	DB59RCASL
	1505A	FSNS59U SNS1P59U DB59U	FSNS59BNCU	DB59BNCU DB59BNCHD 1505ABHD 1505ABHDL	FSNS59RCAU	DB59RCAU
	1505F	FSNS59U SNS1P59U DB59U	FSNS59BNCU	DB59BNCU DB59BNCHD 1505ABHD1 1505ABHDL	FSNS59RCAU	DB59RCAU
	8212	-	FS59BNC SL	DB59BNC SL	FS59RCASL	DB59RCASL
	8221	-	FSNS59BNCU	DB59BNCBU	FSNS59RCAU	DB59RCAU
	8241	-	FSNS59BNCU	DB59BNCBU	FSNS59RCAU	DB59RCAU
	8241A	-	FSNS59BNCU	DB59BNCBU	FSNS59RCAU	DB59RCAU
	8241B	-	FSNS59BNCU	DB59BNCBU	FSNS59RCAU	DB59RCAU
	8241F	-	-	-	-	-
	8263	FSNS59U SNS1P59U DB59U	FSNS59BNCU	DB59BNCU	FSNS59RCAU	DB59RCAU
	8279	-	-	-	-	-
	8281	-	-	DB59SL2-M, DB59SL2-F	-	-
	9100	FSNS59U SNS1P59U DB59U	FSNS59BNCU	DB59BNCU	FSNS59RCAU	DB59RCAU
	9104	FSNS59U SNS1P59U DB59U	FSNS59BNCU	DB59BNCU	FSNS59RCAU	DB59RCAU
	9167	FSNS59U SNS1P59U DB59U	FSNS59BNCU	DB59BNCU	FSNS59RCAU	DB59RCAU
	9240	FSNS59U SNS1P59U -	FS59BNC SL	DB59BNC SL	FS59RCASL	FS59RCASL
	9244	FSNS59U SNS1P59U DB59U	FSNS59BNCU	DB59BNCU	FSNS59RCAU	DB59RCAU
	9259	FSNS59U SNS1P59U DB59U	FSNS59BNCU	DB59BNCU	FSNS59RCAU	DB59RCAU
	9275	FSNS59U SNS1P59U DB59U	FSNS59BNCU	DB59BNCU	FSNS59RCAU	DB59RCAU
	8281B	-	-	DB59SL2-M, DB59SL2-F	-	-
	1505S3	FSNS59U SNS1P59U DB59U	FSNS59BNCU	DB59BNCU DB59BNCHD 1505ABHD1 1505ABHDL	FSNS59RCAU	DB59RCAU
	1505S5	FSNS59U SNS1P59U DB59U	FSNS59BNCU	DB59BNCU DB59BNCHD 1505ABHD1 1505ABHDL	FSNS59RCAU	DB59RCAU
	1505S6	FSNS59U SNS1P59U DB59U	FSNS59BNCU	DB59BNCU DB59BNCHD 1505ABHD1 1505ABHDL	FSNS59RCAU	DB59RCAU
	543945	FSNS59U SNS1P59U DB59U	FSNS59BNCU	DB59BNCU	FSNS59RCAU	DB59RCAU
	549945	FSNS59U SNS1P59U DB59U	FSNS59BNCU	DB59BNCU	FSNS59RCAU	DB59RCAU
RG59 Plenum Center Conductor: .0317 ~ .0399 Dielectric: .130 ~ .137 Outer Jacket: .190 ~ .220	1370P	FS59PL2 DB59PL2/4	FS59BNCPL2	DB59BNCPL2/4	FS59RCAPL2	DB59RCAPL2/4
	1506A	FS59PL2 DB59PL2/4	FS59BNCPL2	DB59BNCPL2/4	FS59RCAPL2	DB59RCAPL2/4
	9104P	FSNS59U SNS1P59U DB59U	FSNS59BNCU	DB59BNCU	FSNS59RCAU	DB59RCAU
	643948	FS59PL2 DB59PL2/4	FS59BNCPL4	DB59BNCPL2/4	FS59RCAPL2	DB59RCAPL2/3/4
	6439C8	FS59PL2 DB59PL2/4	FS59BNCPL2	DB59BNCPL2/4	FS59RCAPL2	DB59RCAPL2/3/4
	649948	FS59PL2 DB59PL2/4	FS59BNCPL2	DB59BNCPL2/4	FS59RCAPL2	DB59RCAPL2/3/4
	82108	FS59PL2 DB59PL2/4	FS59BNCPL2	DB59BNCPL2/4	FS59RCAPL2	DB59RCAPL2/3/4
	82241	-	FS59BNCPL3	DB59BNCPL3	FS59RCAPL3	DB59RCAPL2/3/4
	82259	FS59PL2 DB59PL2/4	FS59BNCPL2	DB59BNCPL2/4	FS59RCAPL2	DB59RCAPL2/3/4
	88241	-	FS59BNCPL3	DB59BNCPL3	FS59RCAPL3	DB59RCAPL2/3/4
	89108	FS59PL4 DB59PL2/4	FS59BNCPL4	DB59BNCPL2/4	FS59RCAPL4	DB59RCAPL2/3/4

Connector/Cable Cross Reference Guide

Cable Part#	F		BNC		RCA	
	SNAP-N-SEAL	DOUBLE-BUBBLE	SNAP-N-SEAL	DOUBLE-BUBBLE	SNAP-N-SEAL	DOUBLE-BUBBLE
						
	CPLCCT-SLM	CPLCRBC-BR	CPLCCT-SLM	CPLCRBC-BR	CPLCCT-SLM	CPLCRBC-BR
RG6 Center Conductor: .0399 ~ .0418 Dielectric: .180 ~ .193 Outer Jacket: .265 ~ .305	1152A	FSNS6U SNS1P6U DB6U	FSNS6BNCU	DB6BNCU	FSNS6RCAU	DB6RCAU
	1189A	FSNS6U SNS1P6U DB6U	FSNS6BNCU	DB6BNCU	FSNS6RCAU	DB6RCAU
	1189AP	FSNS6U SNS1P6U DB6U	FSNS6BNCU	DB6BNCU	FSNS6RCAU	DB6RCAU
	1190A	FSNS6U SNS1P6U DB6U	FSNS6BNCU	DB6BNCU	FSNS6RCAU	DB6RCAU
	1369R	FS6PL2 DB6PL2	FS6BNCPL2	DB6BNCPL2	FS6RCAPL2	DB6RCAPL2
	1530A	FSNS6U SNS1P6U DB6U	FSNS6BNCU	DB6BNCU	FSNS6RCAU	DB6RCAU
	1532A	FSNS6U SNS1P6U DB6U	FSNS6BNCU	DB6BNCU	FSNS6RCAU	DB6RCAU
	1545A	FSNS6U SNS1P6U DB6U	FSNS6BNCU	DB6BNCU	FSNS6RCAU	DB6RCAU
	1546A	FSNS6U SNS1P6U DB6U	FSNS6BNCU	DB6BNCU	FSNS6RCAU	DB6RCAU
	1613A	FSNS6U SNS1P6U DB6U	FSNS6BNCU	DB6BNCU	FSNS6RCAU	DB6RCAU
	1614A	FSNS6U SNS1P6U DB6U	FSNS6BNCU	DB6BNCU	FSNS6RCAU	DB6RCAU
	1694A	FSNS6U SNS1P6U DB6U	FSNS6BNCU	DB6BNCU DB6BNCU DB6BNCHD 1694ABHD1 1694ABHDL	FSNS6RCAU	DB6RCAU
	1829A	FSNS6U SNS1P6U DB6U	FSNS6BNCU	DB6BNCU	FSNS6RCAU	DB6RCAU
	1829AC	FSNS6U SNS1P6U DB6U	FSNS6BNCU	DB6BNCU	FSNS6RCAU	DB6RCAU
	1829R	FSNS6U SNS1P6U DB6U	FSNS6BNCU	DB6BNCU	FSNS6RCAU	DB6RCAU
	1840A	FSNS6U SNS1P6U DB6U	FSNS6BNCU	DB6BNCU	FSNS6RCAU	DB6RCAU
	1841A	FSNS6U SNS1P6U DB6U	FSNS6BNCU	DB6BNCU	FSNS6RCAU	DB6RCAU
	1841AC	FSNS6U SNS1P6U DB6U	FSNS6BNCU	DB6BNCU	FSNS6RCAU	DB6RCAU
	1843A	FSNS6U SNS1P6U DB6U	FSNS6BNCU	DB6BNCU	FSNS6RCAU	DB6RCAU
	7710A	FSNS6U SNS1P6U DB6U	FSNS6BNCU	DB6BNCU	FSNS6RCAU	DB6RCAU
	7711A	FSNS6U SNS1P6U DB6U	FSNS6BNCU	DB6BNCU	FSNS6RCAU	DB6RCAU
	7712A	FSNS6U SNS1P6U DB6U	FSNS6BNCU	DB6BNCU	FSNS6RCAU	DB6RCAU
	7713A	FSNS6U SNS1P6U DB6U	FSNS6BNCU	DB6BNCU	FSNS6RCAU	DB6RCAU
	7915A	FSNS6U SNS1P6U DB6U	FSNS6BNCU	DB6BNCU	FSNS6RCAU	DB6RCAU
	7916A	FSNS6U SNS1P6U DB6U	FSNS6BNCU	DB6BNCU	FSNS6RCAU	DB6RCAU
	9058	FSNS6U SNS1P6U DB6U	FSNS6BNCU	DB6BNCU	FSNS6RCAU	DB6RCAU
	9062	FSNS6U SNS1P6U DB6U	FSNS6BNCU	DB6BNCU	FSNS6RCAU	DB6RCAU
	9066	FSNS6U SNS1P6U DB6U	FSNS6BNCU	DB6BNCU	FSNS6RCAU	DB6RCAU
	9077	FSNS6U SNS1P6U DB6U	FSNS6BNCU	DB6BNCU	FSNS6RCAU	DB6RCAU
	9116	FSNS6U SNS1P6U DB6U	FSNS6BNCU	DB6BNCU	FSNS6RCAU	DB6RCAU
	9116R	FSNS6U SNS1P6U DB6U	FSNS6BNCU	DB6BNCU	FSNS6RCAU	DB6RCAU
	9118	FSNS6U SNS1P6U DB6U	FSNS6BNCU	DB6BNCU	FSNS6RCAU	DB6RCAU
	9248	FSNS6U SNS1P6U DB6U	FSNS6BNCU	DB6BNCU	FSNS6RCAU	DB6RCAU
	9290	FSNS6U SNS1P6U DB6U	FSNS6BNCU	DB6BNCU	FSNS6RCAU	DB6RCAU
	533945	FSNS6U SNS1P6U DB6U	FSNS6BNCU	DB6BNCU	FSNS6RCAU	DB6RCAU
	5339B5	FSNS6U SNS1P6U DB6U	FSNS6BNCU	DB6BNCU	FSNS6RCAU	DB6RCAU
	5339W5	FSNS6U SNS1P6U DB6U	FSNS6BNCU	DB6BNCU	FSNS6RCAU	DB6RCAU
	5399B5	FSNS6U SNS1P6U DB6U	FSNS6BNCU	DB6BNCU	FS6RCAPL2	DB6RCAPL2
	5339Q5	FSNS6U SNS1P6U DB6U	FSNS6BNCU	DB6BNCU	FSNS6RCAU	DB6RCAU
RG6 Plenum Center Conductor: .0399 ~ .0418 Dielectric: .165 ~ .172 Outer Jacket: .220 ~ .250	1369P	FS6PL2 DB6PL2	FS6BNCPL2	DB6BNCPL2	FS6RCAPL2	DB6RCAPL2
	1695A	FS6PL2 DB6PL2	FS6BNCPL2	DB6BNCPL2 DB6BNCPL2 1695ABHD1 1695ABHDL	FS6RCAPL2	DB6RCAPL2
	1829P	FS6PL2 DB6PL2	FS6BNCPL2	DB6BNCPL2	FS6RCAPL2	DB6RCAPL2
	9116P	FS6PL2 DB6PL2	FS6BNCPL2	DB6BNCPL2	FS6RCAPL2	DB6RCAPL2
	633938	FS6PL2 DB6PL2	FS6BNCPL2	DB6BNCPL2	FS6RCAPL2	DB6RCAPL2
	633948	FS6PL2 DB6PL2	FS6BNCPL2	DB6BNCPL2	FS6RCAPL2	DB6RCAPL2
	6339Q8	FS6PL2 DB6PL2	FS6BNCPL2	DB6BNCPL2	FS6RCAPL2	DB6RCAPL2
	639948	FS6PL2 DB6PL2	FS6BNCPL2	DB6BNCPL2	FS6RCAPL2	DB6RCAPL2
	82120	FS6PL2 DB6PL2	FS6BNCPL2	DB6BNCPL2	FS6RCAPL2	DB6RCAPL2
	82248	FS6PL2 DB6PL2	FS6BNCPL2	DB6BNCPL2	FS6RCAPL2	DB6RCAPL2
	89120	FS6PL2 DB6PL2	FS6BNCPL2	DB6BNCPL2	FS6RCAPL2	DB6RCAPL2
	89248	FS6PL2 DB6PL2	FS6BNCPL2	DB6BNCPL2	FS6RCAPL2	DB6RCAPL2

Connector/Cable Cross Reference Guide

Cable Part#		F		BNC		RCA	
		SNAP-N-SEAL		SNAP-N-SEAL			
							
		CPLCCT-L559/11		SNSUNI			
RG11	Center Conductor: .0634 ~ .0647 Dielectric: .280 ~ .294 Outer Jacket: .390 ~ .417	1153A	716SNS1P11H	-	FSNS11BNCU	-	-
		1399A	716SNS1P11H		FSNS11BNCU		
		9764	716SNS1P11H	-	FSNS11BNCU	-	-
		1523A	716SNS1P11H	-	FSNS11BNCU	-	-
		1523R	716SNS1P11H		FSNS11BNCU		
		1525A	716SNS1P11H	-	FSNS11BNCU	-	-
		1617A	716SNS1P11H	-	FSNS11BNCU	-	-
		1618A	716SNS1P11H	-	FSNS11BNCU	-	-
		7731A	716SNS1P11H	-	FSNS11BNCU	-	-
		7983A	716SNS1P11H	-	FSNS11BNCU	-	-
		8213	716SNS1P11H	-	FSNS11BNCU	-	-
		9011	716SNS1P11H	-	FSNS11BNCU	-	-
		9064	716SNS1P11H	-	FSNS11BNCU	-	-
		9292	716SNS1P11H	-	FSNS11BNCU	-	-
		513945	716SNS1P11H	-	FSNS11BNCU	-	-
RG11 Plenum	Center Conductor: .0634 ~ .0647 Dielectric: .280 ~ .294 Outer Jacket: .339 ~ .355	7732A	716SNS1P11HPLA	-	FSNS11HBNCPLA	-	-
		1399P	716SNS1P11HPLA		FSNS11HBNCPLA		
		613948	716SNS1P11HPLA	-	FSNS11HBNCPLA	-	-
		613988	716SNS1P11HPLA	-	FSNS11HBNCPLA	-	-