


**Models 72940, 72941, 72942  
Insulated Scope Probes**



**72940-2, X10 Insulated, 500 MHz, Red**  
(additional photos on page 2)

Insulated Scope Probes for use  
with portable Oscilloscopes.

**Specifications**

Dividing ratio	10:1
Input capacitance	13 pF
Compensation range	10 pF ... 30 pF
Frequency range	0 ... 500 MHz
Rise time	1 ns
Lead length	1.20 m (47 in)
Ground Clip lead length	25 cm (9.75 in)
Ground Clip opening	7 mm (0.25 in)
Input impedance	10 MΩ ± 1 %
Rated voltage	CAT II, 600 V (CAT III, 300 V) (frequency-dependant, see derating curve)


**Features**

- With a Cat II, 600 V (CAT III, 300 V) rating, these probes are perfect for use with portable oscilloscopes.
- And with a 500 MHz bandwidth, these probes provide plenty of headroom for those high frequency measurements.
- Fully Insulated, Meets IEC 61010-031
- Ergonomic Design with Comfort Grip

**Accessories Included**

- Push-on hook clip
- Push-on reference contact
- Reference lead with alligator clip for the connection to the 0.2 mm safety socket in the handle.

**Rating:** CAT II, 600 V (CAT III, 300 V)




**USA:** Sales: 800-490-2361 Fax: 888-403-3360  
**Europe:** 31-(0) 40 2675 150 **International:** 425-446-5500  
**e-mail:** [technicalsupport@pomonatest.com](mailto:technicalsupport@pomonatest.com)

**Where to Buy:** [www.pomonaelectronics.com](http://www.pomonaelectronics.com)

All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.

**Models 72940, 72941, 72942  
Insulated Scope Probes**



**72940-8, X10 Insulated, 500 MHz, Gray**



**72941, Kit Scope Probes, X10 Insulated,  
500 MHz, Red & Gray**

**Ordering Information**

Model Number	Description	Items Included
72940-2	Scope Probe, X10 Insulated, 500 MHz, Red	Red scope probe, black ground lead, red sprung hook, probe tip ground
72940-8	Scope Probe, X10 Insulated, 500 MHz, Gray	Gray scope probe, black ground lead, gray sprung hook, probe tip ground
72941	Kit, Scope Probes, X10 Insulated, 500 MHz, Red & Gray	Red scope probe, gray scope probe, black ground lead, red sprung hook, gray sprung hook, probe tip ground
72942	Probe & Lead Kit for Portable Scopes	72940-2 red scope probe, black ground lead, red sprung hook, probe tip ground, 5907A test leads (straight / right-angle Banana), 5916A and 6041B Alligator Clips, 5910B and 5912B Grabbers, 6146 carrying case



**72942, Probe & Lead Kit for Portable Scopes**

USA: Sales: 800-490-2361 Fax: 888-403-3360  
 Europe: 31-(0) 40 2675 150 International: 425-446-5500  
 e-mail: [technicalsupport@pomonatest.com](mailto:technicalsupport@pomonatest.com)  
 Where to Buy: [www.pomonaelectronics.com](http://www.pomonaelectronics.com)

All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[72940-2](#) [72942](#) [72941](#) [72940-8](#)