




1

ACCEPTS RECEPTACLE CONTACTS 1217378 (#22-#18 AWG SINGLE WIRE), 1217094 (#18-#14 AWG SINGLE WIRE) AND 1217095 (TWO #18'S OR TWO #16'S OR A #16 + #18 COMBINATION).

2

FRONT AND BACK VIEWS SHOW ONLY THE GRIPPERS. FOR KEYING AND POLARIZATION FEATURES, SEE SPECIAL FRONT VIEW.

3

ACCORDING TO IEC 60335-1, GWEPT 750°C WITHOUT FLAME

4

PRELIMINARY - NOT FOR PRODUCTION

5

PREPRODUCTION- FASR REQUIRED

3	—	NATURAL	1C,2D	1B	4	1-521205-2
	—	NATURAL	1A,3A	1C	4	9-521205-3
	—	BLUE	1C,3D	1B	4	1-521205-9
3	—	NATURAL	1C, 3C	3B		1-521205-1
	—	BLACK	NONE	NONE	4	1-521205-0
	—	BLUE	1C,3D	1B		521205-9
	—	BLUE	1C,3D	2A,3B	4	521205-8
	—	NATURAL	1C,3C	3B		521205-7
	03-K	NATURAL	1C,3D	3B		521205-6
	—	BLUE	1C,2D	1B,3A	4	521205-5
	—	BLUE	1D,2C,3D	2A		521205-4
	—	BLUE	NONE	NONE	4	521205-3
	03-A	NATURAL	1C,2D	1B	4	521205-2
	03-A	BLUE	1C,2D	1B		521205-1
	RAST 5 DESIGNATION	FINISH/ COLOR	KEYING FEATURE	POLARIZATION FEATURE		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±	-
1 PLC	±	-
2 PLC	±	0.25 [.010]
3 PLC	±	-
4 PLC	±	-
ANGLES	±	-
FINISH	SEE TABLE	

MATERIAL

NYLON

DWN
JR RUTH
10/20/98

CHK
MS FEHER
10/20/98

APVD
J GILLESPIE
10/20/98

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT

CUSTOMER DRAWING

TE Connectivity

NAME
HOUSING, RECEPT, POSITIVE-LOCK, MKIII, 6.35 [.250] SERIES, 3 POSITION

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=521205

RESTRICTED TO
-

SCALE
4:1

SHEET
1 of 1

REV
G3