



NOTES:

1. ALL DIMENSION IN MM [INCH]
2. GENERAL TOLERANCE: $X.X=\pm 0.4$
 $X.XX=\pm 0.25$
3. TERM. NOS. FOR REF. ONLY
4. CONTACT RATING SWITCHING: 150mA, 250V AC/DC
350mA, 110V AC/DC
5. OPERATING FORCE: 425 ± 100 CM/STANDARD
6. OPERATING TEMP: -30° to 85° C
7. CIRCUIT 4Pole: 3 POSITIONS, 30° INDEX.
8. DIELECTRIC STRENGTH: 1000V RMS min.@SEA LEVEL.
9. **▲** DESIGNATE MAJOR DIMENSIONS
10. HARDWARE SUPPLIED ON SWITCH -SEE BELOW
LOCKING RING, LOCKWASHER, & HEX NUT.



CONTACT CONFIGURATION


Timing: NON-SHORTING



TERMINATION DETAIL

SCALE 2X

▲ HARDWARE SUPPLIED
ON SWITCH



E-SWITCH®

REVISIONS				TITLE			
B	12821	REDRAWN	CJB	2/19/03	SCALE	DATE	DR
A	11516	RELEASED FOR PRODUCTION	RJC	2/13/01	1.5:1	2/13/01	RJC
REV.	ECN No.	DESCRIPTION	DATE	CHKD			DWG
				THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED	KC-43-A-(30.0mm) 01-N-L-S		
							REV
							B