

1.20⁺⁰_{-0.1}



0.80

3.50



17.80^{+0.1}

3.10

SECTION-D



SECTION-B



REDUCED TOP VIEW


AREA IN CONTACT WITH PCB: 220mm²

Part number: HM13238

European Views

www.fciconnect.com		surface	ISO 1302	tolerance std	ISO 406 ISO 1101	projection	mm	
		TOLERANCES UNLESS OTHERWISE SPECIFIED						
Dr	CHAILLEUX	1995/02/22	ANGULAR	0.x	±0.1	size	A2	
Eng	TARON	1995/02/22	LINEAR	0.xx	±0.1	Scale	4	
Chr	LEGARE	1995/02/22	0.xx' ±2'	0.xxx	±0.1	ECN	LS06-0095	
Appr	LEGARE	1995/02/22	Product family	METRAL		Spec ref	-	
rev	ecn no	dr	date	MILLIPACS-1 SHROUD 5 ROWS 120 WAYS				Rev.
B	-	CHA	1996/01/12	SPECIFIC STAND-OFF 8.80mm				C-8626-0607
C	LS05-0038	JTA	2005/04/22	-				E
D	LS05-0084	JTA	2005/09/28	-				
E	LS06-0095	LGO	2006/07/12	-				
-	-	-	-	-				
-	-	-	-	-				
-	-	-	-	-				
-	-	-	-	-				

- NOTE-1: OTHER DIMENSIONS IN ACCORDANCE WITH IEC-48B-(S.296) SPECIFICATION
- NOTE-2: MATERIAL HIGH TEMPERATURE NATURAL COLOUR
- NOTE-3: FORCE FIT CAVITIES FOR RETENTION WITH REAR PLUG-UP CONTACT PART
- NOTE-4: CAVITY FOR LATCHING AND CODING
- NOTE-5: POLARIZING CAVITIES



NOTE-5