

CA1226 Thermo-Anemometer Hotwire, 99k count, dual display, 0.15.



The CA 1226 can be used to check the operation of your ventilation or air-conditioning systems (at the outlet or in the ducts).

Compact and easy to handle, it is equipped with a dual display so that you can simultaneously view two values chosen from the three measured: temperature, speed and the flow.

FUNCTIONS

- Measurement of speed and ambient temperature
- Choice of units
- HOLD Function
- Display of minimum and maximum
- Automatic calculation of the average
- Flow calculation with or without cone
- Adjustable automatic shutdown
- Adjustable backlighting

Specifications:

- Speed: 0.15 to 3 m/s and 3.1 to 30 m/s
- Temperature: -20 to +80 °C
- Flow: 0 to 99,999 m³/h

Operating conditions: 0 to 50 °C; < 85 % RH

Operating atmosphere: neutral gas

Storage conditions: -20 to +80 °C; 15 to 85 % RH

Power supply: 9V 6LR6 alkaline battery

Automatic shutdown function adjustable from 0 to 120 min.

IP 54 protection