

 Active

Always EU RoHS/ELV Compliant (Statement of Compliance)

- ? Connector
- ? Plug
- ? Number of Positions = 26
- ? Wire/Cable Type = Round Jacketed Cable
- ? Wire Range = 0.05 - 0.09 ² [30-28] mm [AWG]

[View all Features](#)

[Check Pricing & Availability](#)
[Search for Tooling](#)
[Product Feature Selector](#)
[Contact Us About This Product](#)

Product Drawings:

Catalog Pages/Data Sheets:

? None Available

Product Specifications:

? None Available

Application Specifications:

? None Available

Instruction Sheets:

? None Available

CAD Files:

? None Available

List all Documents

Additional Information:

? Product Line Information

Related Products:

? Tooling

Product Type Features:

? Product Type = Connector
 ? Gender = Plug
 ? Number of Positions = 26
 ? Wire/Cable Type = Round Jacketed Cable
 ? Wire Insulation Diameter (mm [in]) = 0.74 –
 0.91 [0.029 – 0.036]
 ? Mating Connector Lock = Without
 ? Shielded = No
 ? Detent = Without
 ? Rails = Without
 ? Termination Cover = With
 ? Product Series = Series III
 ? Wire Termination Type = IDC
 ? Termination Cover Type = Standard
 ? Termination Cover Method = Assembled
 ? Color = Black
 ? Plug Shell Material = Steel

Mechanical Attachment:

? Panel Attachment = Without

Termination Related Features:

? Solder Tail Contact Plating = Tin over Nickel

Body Related Features:

? Wire Range (mm [AWG]) = 0.05 - 0.09 ² [30-28]

? Plug Shell Plating = Tin - Nickel Alloy

Contact Related Features:

- ? Contact Material = Phosphor Bronze
- ? Contact Mating Area Plating = Gold Flash over Palladium Nickel, Gold (30) over Nickel (50)

Housing Related Features:

? Housing Material = Nylon, Polyester
? Housing Flammability Rating = UL 94V -0

Industry Standards:

- ? RoHS/ELV Compliance = RoHS compliant, ELV compliant
- ? Lead Free Solder Processes = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

? Terminate To = Wire

Other:

? Brand = Tyco Electronics