




Order Code	TCK-072
Inductance (each winding)	156 μ H $\pm$ 35% (at 100 kHz / 100 mV)
Impedance (DCR)	15 m Ω max.
Rated Current	11.3 A max.
Rated Voltage	500 VDC max. (between windings)
Operating Temperature	-40°C to +105°C



Impedance Curve



Outline Dimensions



Dimensions [mm]

A	16.0 max.
B	16.0 max.
C	15.0 max.
D	4.0 $\pm$ 0.3
E	10.0 $\pm$ 0.3
F	7.4 $\pm$ 0.3
G	$\varnothing$ 0.8