



Plastic Boxes - NEMA 4x
Accessories

Cable glands



Design Features

Required to maintain NEMA 4X rating when cables enter or exit a NEMA 1, 2, 4, 4x, 12 or 13 type enclosure. Assembly consisting of black molded nylon body, hex nut, and cable nut and with a rubber gasket and cable seal. Nylon material has UL94V-2 flammability rating and -40C to 100C suggested service temperature.


Cable Glands			
Catalog Number	Mounting Size	Mounting Hole Diameter	Cable Range
NG-9511	PG-7	.50"	.12"-.26"
NG-9512	PG-9	.61"	.16"-.31"
NG-9513	PG-11	.73"	.20"-.39"
NG-9514	PG-13.5	.81"	.24"-.47"
NG-9515	PG-16	.89"	.39"-.55"
NG-9516	PG-21	1.12"	.51"-.71"
NG-9517	PG-29	1.47"	.71"-.98'

PART
NAME

NEMA 4X GLAND

PART
No.

NG-9511 TO NG-9517



MATERIAL: NYLON -66, UL-94V2 (NUT, BODY & CABLE NUT)
 NBR (N) RUBBER (GASKET & CABLE SEAL)
COLOR: BLACK

PART NO.	MOUNT THREAD	CABLE RANGE (DIA.)	A	B	C	D	E	F	G	H
NG-9511	PG-7	0.118 - 0.256	0.197	0.315	0.488	0.307	1.102	0.039	0.827	0.201
NG-9512	PG-9	0.158 - 0.315	0.283	0.374	0.563	0.307	1.169	0.056	0.921	0.201
NG-9513	PG-11	0.197 - 0.394	0.374	0.512	0.717	0.307	1.236	0.058	1.047	0.201
NG-9514	PG-13.5	0.236 - 0.472	0.453	0.591	0.787	0.346	1.315	0.062	1.161	0.240
NG-9515	PG-16	0.394 - 0.551	0.524	0.669	0.878	0.386	1.425	0.062	1.303	0.240
NG-9516	PG-21	0.512 - 0.709	0.681	0.866	1.102	0.425	1.583	0.062	1.539	0.280
NG-9517	PG-29	0.709 - 0.984	0.957	1.181	1.449	0.425	1.772	0.062	1.972	0.319

PART
NAME

ADAPTER BRACKET

PART
No.

AB-2375

MATERIAL: 16 GA. STEEL
COLOR: BLACK

