

NTE1514 and NTE1515 Integrated Circuit 5-Step LED Driver for Logarithmic Scale

Features:

- Useful for Both AC and DC Level Meter as VU Meter or Signal Meter
- Wide Supply Voltage Range: $V_{CC} = 4.4V$ to $12V$
- DC Amplifier Included

Comparator Level: ($T_A = +25^\circ C$, $V_{CC} = 6V$, $I_{ref} = 5mA$)

Level	Pin	Test Conditions	NTE1514			NTE1515			Unit
			Min	Typ	Max	Min	Typ	Max	
D5	14	$V_{R02} = 2.6V$ to $3V$, $V_{R02} = 0V$	5.5	6.0	6.5	1.6	2.0	2.4	dB
D4	13	$V_{R02} = 2.6V$ to $3V$, $V_{R02} = 0V$	2.5	3.0	3.5	-0.4	0	+0.4	dB
D3	12	$V_{R02} = 2.6V$ to $3V$, $V_{R02} = 0V$	-0.5	0	0.5	-3.6	-3.0	-2.4	dB
D2	11	$V_{R02} = 2.6V$ to $3V$, $V_{R02} = 0V$	-6.0	-5.0	-4.0	-8.0	-7.0	-6.0	dB
D1	10	$V_{R02} = 2.6V$ to $3V$, $V_{R02} = 0V$	-12	-10	-8.0	-17	-15	-13	dB

Note 1. Definition of 0dB: when voltage of OUT_2 is 2.37V ($R_{02} = 3V$, $R_{01} = 0V$).
when voltage of OUT_2 is 1.50V ($R_{02} = 3V$, $R_{01} = 0V$).

Absolute Maximum Ratings: ($T_A = +25^\circ C$ unless otherwise specified)

Maximum Supply Voltage (Pin4), V_{CCmax} -0.3V to +14V
Input Voltage (Pin2, Pin3), V_{IN} -0.3V to +14V
Current at Pin C (Pin1), I_C 0.1mA to 2mA
Output Voltage,
 Pin16 (Note 2), $V_{OUT(1)}$ -0.3V to +12V
 Pin15, $V_{OUT(2)}$ -0.3V to +12V
 Pin10 to Pin14, V_{OUT} -0.3V to 14V
Reference Current (Pin6), I_{ref} 0 to 10mA
Allowable Power Dissipation ($T_A = +55^\circ C$, Total), P_dmax 500mW
Operating Temperature Range, T_{opr} -10° to $+60^\circ C$
Storage Temperature Range, T_{stg} -40° to $+125^\circ C$

Note 2. When OUT_1 is off and OUT_2 is connected to GND (Pin8) through 12k Ω .


Note 3. Notice inhibit to supply any voltage to input and output pin larger than $V_{CC}+0.3V$ (Especially beware of power switch on). Pin D_1 to D_5 should be connected to V_{CC} at no use of LED's.

Allowable Operating Condition: ($T_A = +25^{\circ}\text{C}$ unless otherwise specified)Supply Voltage (Pin4), V_{CC} 4.4 to 12VReference Current (Pin6), I_{ref} 2.5 to 9.0mALoad Resistance (Pin15, inserted between OUT_2 and GND), R_{L2} 15 to 20k Ω **Electrical Characteristics:** ($T_A = +25^{\circ}\text{C}$, $V_{CC} = 4.4\text{V}$ to 12V , $I_{ref} = 5\text{mA}$ unless otherwise specified)

Parameter	Symbol	Pin	Test Conditions	Min	Typ	Max	Unit
Input Bias Current (Amp Section)	$I_{IN+}(A)$	2	$V_{CC} = 12\text{V}$, $V_{IN+} = 10\text{V}$, $V_{IN-} = 0\text{V}$	-2	-	0	μA
	$I_{IN-}(A)$	3	$V_{CC} = 12\text{V}$, $V_{IN+} = 0\text{V}$, $V_{IN-} = 10\text{V}$	-2	-	0	μA
Input Bias Current (Comparator Section)	$I_{IN+}(C)$	5, 7	$V_{CC} = 12\text{V}$, $V_{IN+} = 10\text{V}$, $V_{IN-} = 0\text{V}$, $V_{R01} = 0\text{V}$, $V_{R02} = 0\text{V}$	-10	-	0	μA
	$I_{IN-}(C)$	15	$V_{CC} = 12\text{V}$, $V_{IN+} = 0\text{V}$, $V_{IN-} = 10\text{V}$, $V_{R01} = V_{R02} = V_{ref}$, $V_{OUT2} = 0\text{V}$	-10	-	0	μA
Reference Voltage	V_{ref}	6	$I_{ref} = 2.5\text{mA}$ to 9.0mA	2.6	-	3.0	V
Amp Offset Voltage (Amp Section)	V_{offset}	15	Amp Gain 20dB	-500	-	+500	mV
Output Flow-in Current	$I_{OL(1)}$	16	OUT_1 : $V_{OUT1} = 0.5\text{V}$, $V_{IN+} = 0\text{V}$, $V_{IN-} = 4\text{V}$	0.2	-	-	mA
Output Flow-out Current	$I_{OH(1)}$	16	OUT_1 : $V_{OUT1} = 3.7\text{V}$, $V_{IN+} = 4\text{V}$, $V_{IN-} = 0\text{V}$	-	-	-20	μA
	$I_{OH(2)}$	15	OUT_2 : $V_{CC} = 4.4\text{V}$, $V_{OUT2} = 0\text{V}$	-	-	-3.1	mA
	$I_{OH(2)}$	15	OUT_2 : $V_{CC} = 12\text{V}$, $V_{OUT2} = 0\text{V}$	-	-	-7.0	mA
Output Flow-in Current	$I_{OL(D)}$	10 to 14	D_1 to D_5 : $V_{CC} = 4.4\text{V}$, V_{D1} to $V_{D5} = 2.3\text{V}$, $V_{IN-} = 0\text{V}$, $V_{IN+} = 3\text{V}$, $V_{R02} = 3\text{V}$	3.0	-	7.5	mA
			D_1 to D_5 : $V_{CC} = 12\text{V}$, V_{D1} to $V_{D5} = 9.7\text{V}$, $V_{IN-} = 0\text{V}$, $V_{IN+} = 9\text{V}$, $V_{R02} = 9\text{V}$	3.0	-	7.5	mA
Output Leak Current	$I_{OH(D)}$	10 to 14	D_1 to D_5 : $V_{CC} = 12\text{V}$, $V_{IN+} = 0\text{V}$, $V_{IN-} = 9\text{V}$, $V_{R02} = 9\text{V}$	-	-	50	μA
Current Dissipation	I_{CC}	4	$V_{CC} = 12\text{V}$, $V_{IN+} = 0\text{V}$, $V_{IN-} = 10\text{V}$	-	8	15	mA
Amp Gain	V_G		Open Looped	30	-	-	dB

VU Level Meter

+3dB 0dB -10dB



Input Level

Pin Connection Diagram