



### Features

- RoHS lead-solder-exempt compliant
- Independent dual outputs
- Flexible load sharing
- High efficiency
- Open-frame design
- Planar magnetics
- Independent trim for each output
- Synchronous rectification
- 1500 V isolation
- 100 °C base plate operation

### Description


The TQD dc-dc converters are high power, dual output, fully-isolated converters that feature high efficiency, 1500 VDC isolation, and open-frame packaging. The TQD Series allows board designers to deliver any combination of power from either output, up to each model's maximum rating. The TQD Series is available in 5V/3.3V or 3.3V/2.5V combinations, uses planar magnetics, and has an MTBF of over a million hours.

### Technical Specifications

| Input                            |             |
|----------------------------------|-------------|
| Voltage range                    |             |
| 5 VDC nominal                    | 18 - 36 VDC |
| 12 VDC nominal                   | 36 - 72 VDC |
| Reflected ripple                 | 50 mA       |
| Input Reverse Voltage Protection | Shunt Diode |

| Output                                                                   |                           |
|--------------------------------------------------------------------------|---------------------------|
| Setpoint Accuracy                                                        | ±1%                       |
| Line Regulation $V_{in}$ Min. - $V_{in}$ Max., $I_{out}$ Rated, Output 1 | 0.2% $V_{out}$            |
| Load Regulation $I_{out}$ Min. - $I_{out}$ Max., $V_{in}$ Nom., Output 1 | 0.3% $V_{out}$            |
| Minimum Output Current, Each Output                                      | 10 % $I_{out}$ Rated      |
| Dynamic Regulation, Loadstep                                             | 25% $I_{out}$             |
| Pk Deviation                                                             | 4% $V_{out}$              |
| Settling Time                                                            | 500 $\mu$ s               |
| Voltage Trim Range                                                       | ±10%                      |
| Power Limit Threshold Range, % of $I_{out}$ Rated                        | 110 - 130%                |
| OVP Trip Range                                                           | 115 - 140% $V_{out}$ Nom. |
| UVP Trip Range                                                           | 70 - 90%                  |

| General                        |                           |
|--------------------------------|---------------------------|
| Turn-On Time                   | 20 ms                     |
| Remote Shutdown                | Positive Logic            |
| Switching Frequency            | 250 kHz                   |
| Isolation                      |                           |
| Input - Output                 | 1500 VDC                  |
| Input - Case                   | 1050 VDC                  |
| Output - Case                  | 500 VDC                   |
| Temperature Coefficient        | 0.03 %/°C                 |
| Case Temperature               |                           |
| Operating Range                | -40 To +100 °C            |
| Storage Range                  | -40 To +125 °C            |
| Thermal Shutdown Range         | 105 To 115 °C             |
| Humidity Max., Non-Condensing  | 95%                       |
| Vibration, 3 Axes, 5 Min Each  | 5 g                       |
| MTBF† (Bellcore TR-NWT-000332) | 1.2 X 10 <sup>6</sup> hrs |
| Safety                         | UL, cUL, TUV              |
| Weight (Approx.)               | 3.8 oz                    |



### Notes

† MTBF predictions may vary slightly from model to model.

Specifications typically at 25 °C, normal line, and full load, unless otherwise stated.

Soldering Conditions: I/O pins, 260 °C, ten seconds; fully compatible with commercial wave-soldering equipment.

Units are water-washable and fully compatible with commercial spray or immersion post wave-solder washing equipment.

### Model Selection


| MODEL         | INPUT VOLTAGE (VOLTS) | INPUT VOLTAGE RANGE (VOLTS) | MAXIMUM INPUT CURRENT (AMPS)* | OUTPUT VOLTAGE (VOLTS) | RATED OUTPUT CURRENT (AMPS) | RIPPLE & NOISE pk-pk (mV) | TYPICAL EFFICIENCY** |
|---------------|-----------------------|-----------------------------|-------------------------------|------------------------|-----------------------------|---------------------------|----------------------|
| TQD080ZE2.0-A | 48                    | 36-72                       | 1.9                           | 3.3/2.0                | 15/15                       | 100/75                    | 80%                  |
| TQD085ZED-A   | 48                    | 36-72                       | 2.5                           | 3.3/2.5                | 20/25                       | 100/75                    | 82%                  |
| TQD100ZGE-A   | 48                    | 36-72                       | 3.7                           | 5.0/3.3                | 20/25                       | 100/75                    | 83%                  |

#### NOTES:

- \* Maximum input current at minimum input voltage, maximum rated output power.
- \*\* At nominal  $V_{IN}$ , rated output.
- Current can be drawn from either output to its maximum value, or from both outputs.

Model numbers highlighted in yellow or shaded are not recommended for new designs.

### Mechanical Drawing



| Thermal Impedance                                                                                                                                       |          |
|---------------------------------------------------------------------------------------------------------------------------------------------------------|----------|
| Natural Convection                                                                                                                                      | 5.7 °C/W |
| 100 LFM                                                                                                                                                 | 3.9 °C/W |
| 200 LFM                                                                                                                                                 | 2.6 °C/W |
| 300 LFM                                                                                                                                                 | 1.9 °C/W |
| 400 LFM                                                                                                                                                 | 1.7 °C/W |
| Note:<br>Thermal impedance data is dependent on many environmental factors. The exact thermal performance should be validated for specific application. |          |

| Pin | Function           |
|-----|--------------------|
| 1   | -V <sub>in</sub>   |
| 2   | Enable             |
| 3   | Case               |
| 4   | +V <sub>in</sub>   |
| 5   | +V <sub>out1</sub> |
| 6   | + Sense 1          |
| 7   | Trim 1             |
| 8   | - Sense 1          |
| 9   | -V <sub>out1</sub> |
| 10  | -V <sub>out2</sub> |
| 11  | - Sense 2          |
| 12  | Trim 2             |
| 13  | + Sense 2          |
| 14  | +V <sub>out2</sub> |

| Tolerances                                         |               |
|----------------------------------------------------|---------------|
| Inches:                                            | (Millimeters) |
| .XX ± 0.020                                        | .X ± 0.5      |
| .XXX ± 0.010                                       | .XX ± 0.25    |
| Pin:                                               |               |
| ± 0.002                                            | ± 0.05        |
| (Dimensions as listed unless otherwise specified.) |               |

NUCLEAR AND MEDICAL APPLICATIONS - Power-One products are not authorized for use as critical components in life support systems, equipment used in hazardous environments, or nuclear control systems without the express written consent of the respective divisional president of Power-One, Inc.

TECHNICAL REVISIONS - The appearance of products, including safety agency certifications pictured on labels, may change depending on the date manufactured. Specifications are subject to change without notice.