







REV.	DATE	DESCRIPTION
NC	04/29/99	INITIAL RELEASE
A	07/28/06	UPDATE DRAWING FORMAT



8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex								
7						DRAWN	G.R.S.					07/28/06				
6	FERRULE	COPPER	GOLD	1		CHECKED							PART DESCRIPTION SMA R/A BULKHEAD JACK (FOR RG–58C/U, 58/U CABLE)			
5	HEX NUT	BRASS	GOLD	1		ISSUED										
4	LOCK WASHER	BRASS	GOLD	1		SHEET	1 OF 1		PART NO. 132246							
3	CONTACT PIN	BER. COPPER	GOLD	1												
2	INSULATOR	TEFLON	NATURAL	1		CAD FILE C:/132/132246.DWG			DWG. NO. 132246.DWG				REV. A	SIZE A	SCALE NA	
1	BODY	BRASS	GOLD	1												
DESCRIPTION						MATERIAL	FINISH	QTY								