

Ceramic Substrate / Wave Solderable - InGaN/SiC

INDEX

PRODUCT TREE



WHIP!

Image next to part no. indicates cad file.



Indicates an [Opto Express](#) part.

- [Product Table](#)
- [Reflow Profile / Tape Specification](#)
- [Features/Options](#)
- [Applications/Uses](#)
- [Order Samples](#)
- [Stock/Price Request](#)
- [Sales and Tech Support](#)
- [Drawings](#)

1. [Product Gallery](#)
2. [Surface Mount Leds \(Surfee-Leds\)](#)
3. [Ceramic Carrier](#)
4. [Ceramic Substrate / Wave Solderable - InGaN/SiC](#)

Lumex drawings are in PDF format. If you don't have Adobe Acrobat, click on this icon to

[download a free copy](#)



Lumex Part Number	LED Die Composition	Emitted Color	Peak Wavelength	Lens Color	Axial Intensity If=20mA	Vf Typ @ If=20mA	Vf Max @ If=20mA	View Angle (Degrees)	Reel Size
CCL-CRS10UPG WHIP!	InGaN/SiC	Ultra Pure Green	525	Clear	70	3.5	4.0	180	3000
CCL-CRS10USB WHIP!	InGaN/SiC	Ultra Sup Blue	470	Clear	20	3.5	4.0	180	3000

Reflow Profile / Tape Specification

[\[top of page\]](#)

- All SMTs with a Reflow Profile or Tape Specification can be Found on the WHIP Drawing

Features/Options

[\[top of page\]](#)

- Reliable Ceramic Carriers
- Able to Survive Wave Soldering
- High Reflectivity of Light
- State-of-the-Art LED Die
- Precision Epoxy Casted Lens

Applications/Uses

[\[top of page\]](#)

- Keyboard/Keypad Illumination
- Medical Diagnostic Instruments
- Fault or Status Indicators
- Instrument Control Indicators or Illuminators

[Home](#)

| [What's
New](#)

| [Product
Gallery](#)

| [Product
Search](#)

| [X-Ref Search
Engine](#)

| [Tech
Notes](#)

| [Sales and Tech
Support](#)

| [Corporate
Info](#)

290 East Helen Road Palatine, IL 60067 Telephone: (847) 359-2790 Facsimile: (847) 359-8904 E-mail us at sales@lumex.com

© 1997-2001 Lumex, Inc.