

GR SERIES

RELAY SOCKETS



DESCRIPTION

8 Pin Midget Sockets

ELECTRICAL RATING

- 300 Volts, 10 Amps
- 150 Volts, 15 Amps

CONSTRUCTION

- Contacts** • Brass, Nickel Plated
- Screws** • Binder Head, 6 - 32 x 1/4" Steel, Zinc Plated
- Pressure Clamp, 6- 32 x 5/16" Steel, Zinc Plated, Wire Range #12 - #22 Solid or Stranded
- Molding** • Break Resistant Thermoplastic Black Standard, Grey Available

AGENCY APPROVALS

- UL recognized, File No. E60008
- CSA certified, File No. LR29513
- CE



ORDERING CODE

PART NO.

GR108
GR108-PC

DESCRIPTION

DPDT, 8 Pin Midget
DPDT, 8 Pin Midget

TERMINAL TYPE

Binder Head Screws
Pressure Clamp Screws

ACCESSORIES

PART NO.


HDB-4

DESCRIPTION (Refer to the accessories pages 25-27))


Hold Down Spring



CUSTOM CONNECTOR



TERMINAL LOCATION



TOP VIEW