

HARTING RJ Industrial® IP 20 Standard Patch cables CAT 5e



IP 20 Standard Patch cables
CAT 5e

Advantages

- over moulded RJ45 design with polyamide plastic
- protected locking lever
- suitable for Gigabit Ethernet
- PUR jacket, LSZH
- compact and space saving design for multi-port applications
- RoHS compliant

General

The HARTING standard patch cables are designed for Industrial Ethernet cabling systems in an environment of limited mechanical stress. Applications in control cabinets require high-quality cables with small but robust connectors. For this reason the HARTING standard patch cables are especially designed for multi-port switches and compact industrial devices. HARTING's standard patch cables are deployable for safe Gigabit Ethernet transmission.

Description

Order number


IP 20 Standard Patch cables CAT 5e

green 0.5 m
green 1.0 m
green 1.5 m
green 2.0 m
green 2.5 m
green 3.0 m
green 4.0 m
green 5.0 m
green 7.5 m
green 10.0 m
green 15.0 m
green 20.0 m

black 0.5 m
black 1.0 m
black 1.5 m
black 2.0 m
black 2.5 m
black 3.0 m
black 4.0 m
black 5.0 m
black 7.5 m
black 10.0 m
black 15.0 m
black 20.0 m

09 45 971 1101
09 45 971 1102
09 45 971 1115
09 45 971 1103
09 45 971 1116
09 45 971 1104
09 45 971 1105
09 45 971 1106
09 45 971 1109
09 45 971 1112
09 45 971 1113
09 45 971 1114

09 45 971 1121
09 45 971 1122
09 45 971 1135
09 45 971 1123
09 45 971 1136
09 45 971 1124
09 45 971 1125
09 45 971 1126
09 45 971 1129
09 45 971 1132
09 45 971 1133
09 45 971 1134



- Cable SF/UTP AWG 26/7
- PUR chemical resistant cable jacket
- 100% electrical tested @ 500VDC/min
- option of green and black cable

All data given are in line with the actual state of art and therefore not binding.
HARTING reserves the right to modify designs without giving the relevant reasons.

Technical Characteristics

Performance	Category 5e acc. to ISO/IEC 11801:2002-09
Mechanical Characteristics	
Retention Force	min. 50N
Electrical Characteristics	
Impedance	100 Ohm
Environmental Characteristics	
Protection class	IP 20
Lead free	LSZH and RoHS compliant
Thermal Characteristics	
Operating temperature	- 20°C to + 60°C