

PVC Strain Relief for rewirable connectors

**Description**

- 1 Function:
- Press-Fit Version
- bend protection for cable

Weblinks

[pdf-datasheet](#), [html-datasheet](#), [General Product Information](#), [Approvals](#), [RoHS](#), [CHINA-RoHS](#), [Mating Connectors](#), [e-Shop](#), [SCHURTER-Stock-Check](#), [Distributor-Stock-Check](#), [CAD-Drawings](#), [Accessories](#), [Detailed request for product](#)

Variants

Suitable for	Color	Für Leitung mit Mantelaus- senddurchmesser	Tüllenlänge [mm]	Order Number
1651 , 4013 , 4020 , 4021 , 4022 , 8101 , 8111 , 9009 , 9009-New , 9013	white	8.7 mm	39.4	4311.0053
0104 , 0104U , 0106	white	10 mm	39	4311.0063
0104 , 0104U , 0106	white	8 mm	38	4311.0064
4012	white	8 mm	37.5	4311.0067
1651 , 4013 , 4020 , 4021 , 4022 , 8101 , 8111 , 9009 , 9009-New , 9013	white	10 mm	39	4311.0068
0104 , 0104U , 0106	black	8 - 10 mm	40.3	4311.9301
0104 , 0104U , 0106	grey	8 - 10 mm	40.3	4311.9302
1651 , 4013 , 4020 , 4021 , 4022 , 8101 , 8111 , 9009 , 9009-New , 9013	black	8.7 - 10 mm	40.3	4311.9305
1651 , 4013 , 4020 , 4021 , 4022 , 8101 , 8111 , 9009 , 9009-New , 9013	grey	8.7 - 10 mm	40.3	4311.9306
4012	black	8 - 10 mm	36.7	4311.9307
1251	black	6.5 mm	30	4311.9309
0101 , 0102 , 0104 , 0104U , 0106 , 0112	black	8 mm	38	4311.9310
0101 , 0102 , 0112	black	10 mm	40	4311.9313
0104 , 0104U , 0106	grey	10 mm	39	4311.9315
1651 , 4013 , 4020 , 4021 , 4022 , 8101 , 8111 , 9009 , 9009-New , 9013	black	8.7 mm	39.4	4311.9316
1651 , 4013 , 4020 , 4021 , 4022 , 8101 , 8111 , 9009 , 9009-New , 9013	grey	8.7 mm	39.4	4311.9317
1651 , 4013 , 4020 , 4021 , 4022 , 8101 , 8111 , 9009 , 9009-New , 9013	black	10 mm	39	4311.9318
1651 , 4013 , 4020 , 4021 , 4022 , 8101 , 8111 , 9009 , 9009-New , 9013	grey	10 mm	39	4311.9319
4012	black	8 mm	37.5	4311.9320
4012	grey	8 mm	37.5	4311.9321
4012	black	10 mm	37	4311.9322
1251	white	6.5 mm	30	4311.9324

Packaging unit 100 Pcs