


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
		P	LTR	DESCRIPTION	DAP
G	14		C1	REVISED PER ECR 09-023200	27OCT09 JR TM



AMP WIRE RANGE	Listed FILE E13288	LR7189 Certified
16-14 AWG STRANDED	16-14 AWG STRANDED	NOT CERTIFIED

- 1 STAMP AMP 16-14*, APPROX AS SHOWN
- 2 COPPER PER ASTM B-152, ANNEALED
- 3 0.00254 [0.000100] MIN TIN PER ASTM B-545



35116

PART NUMBER

CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX		THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN 1-28-93 TA BRINKMAN		Tyco Electronics Corporation Harrisburg, PA 17105-3608		
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: N/A		DIMENSIONS: MM [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK 1-28-93 DA PATTERSON		NAME	
	FOR APPLICATION TOOLING ASSISTANCE CENTER		CIRCULAR MIL AREA: 1.04-2.62mm² [2,050-5,180]				0 PLC ± -		APVD 1-28-93 JL MECKLEY		TERMINAL, SPADE	
	TOOLING INFORMATION 1-800-722-1111		STRANDED				1 PLC ± -		PRODUCT SPEC		TONGUE, BUDGET	
							2 PLC ± 0.20 [.008]		APPLICATION SPEC		-	
					MATERIAL		4 PLC ± -		WEIGHT		SIZE	
					-		ANGLES ± -		-		CAGE CODE	
							FINISH		-		DRAWING NO	
							-		CUSTOMER DRAWING		RESTRICTED TO	
											A2 00779 C=35116	
											SCALE	
											10:1	
											SHEET	
											1 of 1	
											REV	
											C1	