



Fiberglass Omnidirectional Wireless Antennas

[Stock Locator](#)

- Includes VHF through 2.4 GHz models
- High performance and reliable collinear J-pole design surrounded by durable high density fiberglass
- Durable gold anodized sleeve and cap will not oxidize
- Custom tuning available
- FedEx/UPS shippable on most models

Results 1 - 65 of 65

Item #	Model	Frequency Range	Tuned Frequency	Gain	Length	Max. Power
FG1400	VHF Models	140 - 144 MHz	142 MHz	Unity	92 inches	150 watts
FG1403	VHF Models	140 - 144 MHz	142 MHz	3 dBD	107 inches	150 watts
FG1440	VHF Models	144 - 148 MHz	146 MHz	Unity	92 inches	150 watts
FG1443	VHF Models	144 - 148 MHz	146 MHz	3 dBD	107 inches	150 watts
FG1480	VHF Models	148 - 152 MHz	150 MHz	Unity	68 inches	150 watts
FG1483	VHF Models	148 - 152 MHz	150 MHz	3 dBD	107 inches	150 watts
FG1520	VHF Models	152 - 156 MHz	154 MHz	Unity	68 inches	150 watts
FG1523	VHF Models	152 - 156 MHz	154 MHz	3 dBD	107 inches	150 watts
FG1560	VHF Models	156 - 162 MHz	159 MHz	Unity	68 inches	150 watts
FG1563	VHF Models	156 - 162 MHz	159 MHz	3 dBD	107 inches	150 watts
FG1620	VHF Models	162 - 168 MHz	165 MHz	Unity	68 inches	150 watts
FG1623	VHF Models	162 - 168 MHz	165 MHz	3 dBD	107 inches	150 watts
FG1683	VHF Models	168 - 174 MHz	171 MHz	3 dBD	107 inches	150 watts
FG2200	VHF Models	220 - 225 MHz	222.5 MHz	Unity	68 inches	150 watts
FG2203	VHF Models	220 - 225 MHz	222.5 MHz	3 dBD	83.5 inches	150 watts
FG3603	UHF Models	360 - 380 MHz	370 MHz	3 dBD	44 inches	100 watts
FG3803	UHF Models	380 - 390 MHz	385 MHz	3 dBD	44 inches	100 watts
FG4060	UHF Models	406 - 416 MHz	411 MHz	Unity	26 inches	100 watts
FG4063	UHF Models	406 - 416 MHz	411 MHz	3 dBD	44 inches	100 watts
FG4065	UHF Models	406 - 416 MHz	411 MHz	5 dBD	76 inches	100 watts
FG4100	UHF Models	410 - 430 MHz	420 MHz	Unity	26 inches	100 watts
FG4103	UHF Models	410 - 420 MHz	415 MHz	3 dBD	44 inches	100 watts
FG4203	UHF Models	420 - 430 MHz	425 MHz	3 dBD	44 inches	100 watts
FG4205	UHF Models	420 - 430 MHz	425 MHz	5 dBD	76 inches	100 watts
FG4300	UHF Models	430 - 450 MHz	440 MHz	0 dBD	26 inches	100 watts
FG4303	UHF Models	430 - 440 MHz	435 MHz	3 dBD	44 inches	100 watts
FG4305	UHF Models	430 - 440 MHz	435 MHz	5 dBD	76 inches	100 watts
FG4403	UHF Models	440 - 450 MHz	445 MHz	3 dBD	44 inches	100 watts
FG4405	UHF Models	440 - 450 MHz	445 MHz	5 dBD	76 inches	100 watts
FG4500	UHF Models	450 - 470 MHz	460 MHz	Unity	26 inches	100 watts
FG4503	UHF Models	450 - 460 MHz	455 MHz	3 dBD	44 inches	100 watts
FG4505	UHF Models	450 - 460 MHz	455 MHz	5 dBD	76 inches	100 watts
FG4505W	UHF Models	450 - 470 MHz	460 MHz	5 dBD	76 inches	100 watts
FG4507	UHF Models	450 - 460 MHz	455 MHz	7 dBD	107 inches	100 watts
FG4603	UHF Models	460 - 470 MHz	465 MHz	3 dBD	44 inches	100 watts
FG4605	UHF Models	460 - 470 MHz	465 MHz	5 dBD	76 inches	100 watts

FG4607	UHF Models	460 - 470 MHz	465 MHz	7 dBD	107 inches	100 watts
FG4705	UHF Models	470 - 480 MHz	475 MHz	5 dBD	76 inches	100 watts
FG4900	UHF Models	490 - 512 MHz	501 MHz	Unity	26 inches	100 watts
FG4907	UHF Models	490 - 500 MHz	495 MHz	7 dBD	107 inches	100 watts
FG5003	UHF Models	500 - 512 MHz	506 MHz	3 dBD	44 inches	100 watts
FG5007	UHF Models	500 - 512 MHz	506 MHz	7 dBD	107 inches	100 watts
FG7463	700 - 900 MHz Models	746 - 796 MHz	771 MHz	3 dBD	23 1/2 inches	100 watts
FG7466	700 - 900 MHz Models	746 - 796 MHz	771 MHz	6 dBD	61 inches	100 watts
FG8060	700 - 900 MHz Models	806 - 866 MHz	813.5 MHz	Unity	15 inches	100 watts
FG8063	700 - 900 MHz Models	806 - 866 MHz	813.5 MHz	3 dBD	25 inches	100 watts
FG8063WPTNF	700 - 900 MHz Models	806 - 896 MHz	851 MHz	3 dBD	29 inches	100 watts
FG8066	700 - 900 MHz Models	806 - 866 MHz	813.5 MHz	6 dBD	65 inches	100 watts
FG8240	700 - 900 MHz Models	824 - 896 MHz	835 MHz	Unity	15 inches	100 watts
FG8243	700 - 900 MHz Models	824 - 896 MHz	835 MHz	3 dBD	25 inches	100 watts
FG8246	700 - 900 MHz Models	824 - 896 MHz	835 MHz	6 dBD	65 inches	100 watts
FG8693	700 - 900 MHz Models	869 - 902 MHz	882 MHz	3 dBD	25 inches	100 watts
FG8960	700 - 900 MHz Models	896 - 940 MHz	898 MHz	Unity	15 inches	100 watts
FG8963	700 - 900 MHz Models	896 - 940 MHz	898 MHz	3 dBD	25 inches	100 watts
FG8966	700 - 900 MHz Models	896 - 940 MHz	898 MHz	6 dBD	65 inches	100 watts
FG9023	700 - 900 MHz Models	902 - 928 MHz	915 MHz	3 dBD	25 inches	100 watts
FG9026	700 - 900 MHz Models	902 - 928 MHz	915 MHz	6 dBD	65 inches	100 watts
FG9283	700 - 900 MHz Models	928 - 970 MHz	930 MHz	3 dBD	25 inches	100 watts
FG9360	700 - 900 MHz Models	936 - 970 MHz	953 MHz	Unity	15 inches	100 watts
FG9286	700 - 900 MHz Models	928 - 970 MHz	930 MHz	6 dBD	65 inches	100 watts
FG9366	700 - 900 MHz Models	936 - 970 MHz	953 MHz	6 dBD	65 inches	100 watts
FG24005	2.4 GHZ Models	2400 - 2500 MHz	2450 MHz	5 dBi	14 inches	100 watts
FG24008	2.4 GHZ Models	2400 - 2500 MHz	2450 MHz	8 dBi	24 inches	100 watts
FG821/18503	Dual Band Model	1850 - 1990 MHz 821 - 896 MHz	858.5 MHz 1920 MHz	Unity 3 dBD	14 inches	100 watts
FG16397	FG16397	806 - 896 MHz 890 - 960 MHz 1850 - 1990 MHz 2400 - 2500 MHz	N/A	2 dBi 1 dBi 3.3 dBi 2 dBi	14 inches	100 watts

Results 1 - 65 of 65