

REDINGTON COUNTERS, INC.  
P.O. Box 608, 130 Addison Road, Windsor, CT 06095  
Toll Free: (860) 688-6205 • Fax: 860/688-1591  
E-Mail: Info@RedingtonCounters.com • Website: www.RedingtonCounters.com

## Item # 1-4645, Right-hand, top-going, standard reset knob



### Right-hand, top-going, standard reset knob

These 5 figure stroke counters are especially designed for limited space and high count life applications. The advanced drive system translates into exceptionally high operating speeds, extended operating life, for fast and accurate readings. Ideal for copiers, printing presses, cut-off machines, and piece-part counting applications. Also available with a thumb lever for use as a tally counter.

## SPECIFICATIONS

Model No.	46
Display	5 Figures, white on black, 0.19 inch (5mm) high
Display Height	0.19 Inch
Display Height	5 mm
No. of Digits	5
Reset Type	Standard knob
Speed	500 counts/minute
Operating Temperature	-15 to +140 °F
Operating Temperature	-25 to +60 °C
Mounting Hole Dia.	0.13 x 0.24 Inch
Mounting Hole Dia.	3.3 x 6.1 mm
Weight	2 oz
Weight	57 gm
Stock Availability	Yes
Operating Life	Beyond 5 million counts
Rotation	Top-going
Shaft Extension	Right-hand
Shaft Diameter	0.156 Inch
Shaft Diameter	4.0 mm
Minimum Count Stroke	40 °

Maximum Count Stroke	45 &#176
----------------------	----------