



T 5 Ø 16 mm

- **E 14**
16,0 x 54,0
Sockel DIN 49615
- **BA 15d**
16,0 x 54,0
Sockel DIN 49720



E 14



BA 15d

Spannung Voltage	Stromstärke Current	Leistung Power	Lichtstärke Light intensity	Lebensdauer Lifetime	Bestellcode Ordering Code	
V	mA	Watt	MSCP	(h) AC	1654 40 ..	1654 50 ..
6-7	700	4,00	2,000	1.500		1654 50 0607 04
12	410	5,00	1,600	2.000	1654 40 012 005	
24	166	4,00	1,600	5.000	1654 40 024 004	
24	210	5,00	2,000	4.000	1654 40 024 005	1654 50 024 005
24	290	7,00	3,400	4.000	1654 40 024 007	1654 50 024 007
24	420	10,00	4,800	1.500		1654 50 024 010
24-30	166	4,00	1,600	1.500		1654 50 2430 04
30	100	3,00	1,200	4.000	1654 40 030 003	
30	166	5,00	2,400	4.000	1654 40 030 005	1654 50 030 005
60	117	7,00	3,000	4.000	1654 40 060 007	
110-130	30	3-5	0,800	5.000		1654 50 1113 35
110-130	64	7-10	2,000	5.000	1654 40 1113 71	1654 50 1113 71
110-130	36	4,00	1,200	5.000		1654 50 1113 04
130	38	5,00	1,500	5.000		1654 50 130 005
220-260	18	4-6	0,500	6.000		1654 50 2226 46
220-260	23	5-7	0,800	5.000	1654 40 2226 57	1654 50 2226 57
220-260	32	7-10	1,600	5.000	1654 40 2226 71	1654 50 2226 71

