




TRANSLOCK® MINI KEYLESS LOCKING BUSHES METRIC SERIES



RS Article no.	Bore d mm	Outside diameter D mm	Dimensions mm				Rated Loads		Hub Pressure N/cm ²	Nut Torque Nm	Approx. Weight kg
			L1	L2	W	B	Torque Nm	Thrust N			
7784935	5	16	19	9.5	13	3	11.8	3180	3600	14.1	0.014
7784938	6	16					15.7	3580			
7784932	7	19	22	11	16	3	20.1	3830	2600	17	0.028
7784941	8	19					22.9	4050			
7784944	9	19					26.1	4180			
7784948	10	22.5	25.5	12.5	19	5	30.2	4250	1900	20.1	0.042
7784957	11	22.5					34.1	4330			
7784950	12	22.5					39.0	4390			
7784954	14	25.5	28.5	16	22	5	43.9	4490	1300	23.4	0.056
7784963	15	25.5					45.1	4510			
7784966	16	25.5					53.0	4530			
7784960	17	32	35	19	27	6	170.2	9020	5850	39.5	0.230