


Signal lamps with integrated filament/neon lamp - 7 mm



Pict.: yellow

Mounting hole

Technical Data

General information

Form of lens	round
Colour of lens	see order block
Diameter of collar	8.5

Dimensions

Overall height	5 mm
Mounting depth	see order block
Mounting hole	7 mm

Mechanical design

Mounting	pressing into hole
Terminals	see order block
Lamp socket	no
Lamp	see order block

Electrical characteristics

Voltage limit max.	see order block
Power limit max.	see order block

Other specifications

Operating life	see order block
Degree of protection from front side	IP40
Weight	0.87 g

3


integr.
Lamp

Approvals



VDET85° (only version with neon lamp)

Signal lamps with integrated filament/neon lamp - 7 mm, solder terminals



Voltage limit max.	Power limit max.	Terminals	Lamp	Operating life	Colour of lens	Order no.
24 V	0.84 W	solder terminals	filament lamp	25,000 h	transparent colourless	1.69.511.054/1002
24 V	0.84 W	solder terminals	filament lamp	25,000 h	transparent red	1.69.511.054/1301
24 V	0.84 W	solder terminals	filament lamp	25,000 h	transparent yellow	1.69.511.054/1402
24 V	0.84 W	solder terminals	filament lamp	25,000 h	transparent green	1.69.511.054/1502
230 V	-	solder terminals	neon lamp	-	transparent colourless	1.69.511.059/1002
230 V	-	solder terminals	neon lamp	-	transparent red	1.69.511.059/1301
230 V	-	solder terminals	neon lamp	-	transparent yellow	1.69.511.059/1402

Technical data see page 3 - 28

Other voltages on request.

3

integr.
Lamp