



818-341-3355 | info@nmbtc.com
Quality Is Our Primary Component

Search

PRODUCTS

INDUSTRIES

ENGINEERING

DISTRIBUTION

PRESS & ARTICLES

COMPANY

CONTACT

RSS Feed

Fans and Blowers

Fans & Blowers Search

[Motorized Impellers](#)

[AC Weather Resistant](#)

White Papers

Part Numbering

Engineering Info

Cross Reference

Find Inventory

Distributors

Fan Accessories

RoHS

FAQs

Contact

AC Axial Fans Part Numbering System

AC Axial Fans Part Numbering System

To show details, place the mouse cursor on each item of the part number. Click "Display All" button to show all details.

47 (1)	15 (2)	M (3)	S (4)	-	12 (5)	T (6)	-	B (7)	2 (8)	0 (9)	-	A (10)	00 (11)	Display All
1. Size				2. Thickness				3. Series		4. Motor Type				
24			60mm									P series	S	Shaded Pole
31			80mm			10			25mm					
36			92mm			12			30mm			M series	C	Capacitor Run
47			119mm			15			38mm					
59			150mm											
5. Input Voltage				6. Termination		7. Bearing		8. Speed						
100V class		200V class												
10	100V	20	200V		W	Lead Wires	B	Ball Bearing				1 < 2 < 3 < 4 < 5		
12	115V	22	220V		T	Terminal						low	high	
		23	230V											
		24	240V											
9. Protection				10. Product Number				11. Individual Specification						
0	Impedance Protected			A	Standard 115V, 230V & 240V			00	Standard					
				B	Standard 100V, 200V & 220V			01-99	Custom					
A	Thermal Protected			D	Custom casing, 115V-230V									
	(including 5915PC B30 only)			K	Frameless									