

1		2		3		4		5		6		7																																		
										Signature Sean		Revision History For Bulk Production																																		
												Date Aug.15.2014																																		
												Rev. 01																																		
A	RoHS Compliant												A																																	
B	USB 3.0 A TYPE MALE												B																																	
C	USB 3.0 A TYPE MALE												C																																	
D	NOTES: 1.CABLE: UL 2725 [28AWG(7/0.127TC)*1P+D28AWG(7/0.127TC)+AL/MY]*2C+28AWG(7/0.127TC)*1P+28AWG(7/0.127TC)*2C +D28AWG(7/0.127TC)+AL/MY+B(85% COVERAGE ALM) OD=5.5±0.20mm JACKET COLOR: BLACK CABLE MUST PRINT: E***** AWM STYLE 2725 80°C 30V VW-1 2.CONNECTOR: P1&P2 : USB 3.0 A/M, SOLDER, BLUE INSULATION, 3u GOLD PLATED CONTACTS, NICKEL PLATED SHELL 3.HOOD: MOLDED TYPE,PVC 45P,COLOR:BLACK. 4.ELECTRICLE TEST: (1)100% OPEN SHORT & MIS WIRE TEST. (2)CONTACT RESISTANCE 3 ohm Max . (3)INSULATION RESISTANCE 10M ohm Min . (4)HI-POT TEST:DC 300V/10ms												D																																	
E	PIN ASSIGNMENT <table><tr><td>P1</td><td>RED</td><td>P2</td></tr><tr><td>1</td><td>WHITE</td><td>1 VCC</td></tr><tr><td>2</td><td>GREEN</td><td>2 -DATA</td></tr><tr><td>3</td><td>BLACK</td><td>3 +DATA</td></tr><tr><td>4</td><td>BLUE</td><td>4 GND_PWRrt</td></tr><tr><td>5</td><td>YELLOW</td><td>5 SDP1-</td></tr><tr><td>6</td><td>D.W</td><td>6 SDP1+</td></tr><tr><td>7</td><td>PURPLE</td><td>7 SDP1,SDP2_Drain</td></tr><tr><td>8</td><td>ORANGE</td><td>8 SDP2-</td></tr><tr><td>9</td><td>B.D</td><td>9 SDP2+</td></tr><tr><td>SHELL</td><td></td><td>SHELL</td></tr></table>												P1	RED	P2	1	WHITE	1 VCC	2	GREEN	2 -DATA	3	BLACK	3 +DATA	4	BLUE	4 GND_PWRrt	5	YELLOW	5 SDP1-	6	D.W	6 SDP1+	7	PURPLE	7 SDP1,SDP2_Drain	8	ORANGE	8 SDP2-	9	B.D	9 SDP2+	SHELL		SHELL	E
P1	RED	P2																																												
1	WHITE	1 VCC																																												
2	GREEN	2 -DATA																																												
3	BLACK	3 +DATA																																												
4	BLUE	4 GND_PWRrt																																												
5	YELLOW	5 SDP1-																																												
6	D.W	6 SDP1+																																												
7	PURPLE	7 SDP1,SDP2_Drain																																												
8	ORANGE	8 SDP2-																																												
9	B.D	9 SDP2+																																												
SHELL		SHELL																																												
F	Cross Section:												F																																	
G	<table><tr><td>Part No.</td><td colspan="2">AK-300114-010-S</td></tr><tr><td>EAN:4016032283201</td><td colspan="2"></td></tr><tr><td>Title</td><td colspan="2">USB 3.0 A/M - A/M CABLE</td></tr><tr><td>Scale</td><td>N/A</td><td>Sheet</td></tr><tr><td>Unit</td><td>MM</td><td>1/2</td></tr></table>												Part No.	AK-300114-010-S		EAN:4016032283201			Title	USB 3.0 A/M - A/M CABLE		Scale	N/A	Sheet	Unit	MM	1/2	G																		
Part No.	AK-300114-010-S																																													
EAN:4016032283201																																														
Title	USB 3.0 A/M - A/M CABLE																																													
Scale	N/A	Sheet																																												
Unit	MM	1/2																																												
H	ASSMANN Electronic GmbH												H																																	
1		2		3		4		5		6		7																																		

	1	2	3	4	5	6	7																													
A	Package Details					Signature		Revision History		Date	Rev.																									
						LIBRA		For Bulk Production		Aug.15.2014	01																									
B	Single Cable					Single Cable																														
C	<table><tr><th>P/N</th><th>Cable Length</th><th>Rolling Size (Single Cable)</th><th>Polybag Type (Single Cable)</th><th>Bag Size (Single Cable)</th><th>Article Weight (Single Cable)</th></tr><tr><td>AK-300114-010-S</td><td>1.0m</td><td>mm max.</td><td>Ordinary Polybag (Heat Sealed)</td><td>*0.05mm</td><td>kg</td></tr></table>					P/N	Cable Length	Rolling Size (Single Cable)	Polybag Type (Single Cable)	Bag Size (Single Cable)	Article Weight (Single Cable)	AK-300114-010-S	1.0m	mm max.	Ordinary Polybag (Heat Sealed)	*0.05mm	kg	<table><tr><td rowspan="2">40MM</td><td rowspan="2"> 50mm USB 3.0 connection cable, type A M/M, 1.0m, USB 3.0 conform, UL, bl P/N: AK-300114-010-S 4 0 1 6 0 3 2 2 8 3 2 0 1 Assmann Electronic GmbH, Auf dem schüffel 3, 58513 Lüdenscheid. www.assmann.com </td><td rowspan="2"> HEAT SEALED HOLE </td></tr><tr></tr></table>						40MM	50mm USB 3.0 connection cable, type A M/M, 1.0m, USB 3.0 conform, UL, bl P/N: AK-300114-010-S 4 0 1 6 0 3 2 2 8 3 2 0 1 Assmann Electronic GmbH, Auf dem schüffel 3, 58513 Lüdenscheid. www.assmann.com	HEAT SEALED HOLE										
	P/N	Cable Length	Rolling Size (Single Cable)	Polybag Type (Single Cable)	Bag Size (Single Cable)	Article Weight (Single Cable)																														
AK-300114-010-S	1.0m	mm max.	Ordinary Polybag (Heat Sealed)	*0.05mm	kg																															
40MM	50mm USB 3.0 connection cable, type A M/M, 1.0m, USB 3.0 conform, UL, bl P/N: AK-300114-010-S 4 0 1 6 0 3 2 2 8 3 2 0 1 Assmann Electronic GmbH, Auf dem schüffel 3, 58513 Lüdenscheid. www.assmann.com	HEAT SEALED HOLE																																		
D	Inner Packing Unit					Inner Packing Unit																														
E	<table><tr><th>P/N</th><th>Cable Length</th><th>Quantity (Inner Packing Unit)</th><th>Type (Inner Packing Unit)</th><th>Size (Inner Packing Unit)</th><th>Weight (Inner Packing Unit)</th></tr><tr><td>AK-300114-010-S</td><td>1.0m</td><td>10 pcs</td><td>Polybag (Heat Sealed)</td><td>*0.05mm</td><td>kg</td></tr></table>					P/N	Cable Length	Quantity (Inner Packing Unit)	Type (Inner Packing Unit)	Size (Inner Packing Unit)	Weight (Inner Packing Unit)	AK-300114-010-S	1.0m	10 pcs	Polybag (Heat Sealed)	*0.05mm	kg	<table><tr><td rowspan="2">45mm</td><td rowspan="2"> 70mm P/N:AK-300114-010-S QTY:10pcs 4 0 1 6 0 3 2 2 8 3 2 0 1 </td><td rowspan="2"> HEAT SEALED </td></tr><tr></tr></table>						45mm	70mm P/N:AK-300114-010-S QTY:10pcs 4 0 1 6 0 3 2 2 8 3 2 0 1	HEAT SEALED										
	P/N	Cable Length	Quantity (Inner Packing Unit)	Type (Inner Packing Unit)	Size (Inner Packing Unit)	Weight (Inner Packing Unit)																														
AK-300114-010-S	1.0m	10 pcs	Polybag (Heat Sealed)	*0.05mm	kg																															
45mm	70mm P/N:AK-300114-010-S QTY:10pcs 4 0 1 6 0 3 2 2 8 3 2 0 1	HEAT SEALED																																		
F	Order No: Item No: EAN-Code: QTY: N.W.: G.W.: Order: PCS KGS KGS ROTTERDAM C/NO: MANUFACTURED IN P.R.C																																			
G											<table><tr><td rowspan="3">Drawn by</td><td>Date</td><td>Name</td><td rowspan="3">Part No.</td></tr><tr><td>Aug.15,2014</td><td>Sean</td><td rowspan="2">AK-300114-010-S</td></tr><tr><td>Checked by</td><td>Aug.15,2014</td><td>Joe</td></tr><tr><td>Approved by</td><td>Aug.15,2014</td><td>Andy</td><td colspan="2">Title</td></tr><tr><td colspan="3" rowspan="3">ASSMANN Electronic GmbH</td><td colspan="2">USB 3.0 A/M - A/M CABLE</td></tr><tr><td>Scale</td><td>N/A</td><td rowspan="2">Sheet 2/2</td></tr><tr><td>Unit</td><td>MM</td></tr></table>						Drawn by	Date	Name	Part No.	Aug.15,2014	Sean	AK-300114-010-S	Checked by	Aug.15,2014	Joe	Approved by	Aug.15,2014	Andy	Title		ASSMANN Electronic GmbH			USB 3.0 A/M - A/M CABLE	
Drawn by	Date	Name	Part No.																																	
	Aug.15,2014	Sean		AK-300114-010-S																																
	Checked by	Aug.15,2014			Joe																															
Approved by	Aug.15,2014	Andy	Title																																	
ASSMANN Electronic GmbH			USB 3.0 A/M - A/M CABLE																																	
			Scale	N/A	Sheet 2/2																															
			Unit	MM																																
H	* "ROTTERDAM" is for Sea Freight shipment * "COLOGNE" is for Air Freight shipment * "LUDENSCHIED" is for Fedex or UPS shipment																																			
	1	2	3	4	5	6	7																													