






NOTES:

- 1) CAPACITANCE (1000hrs.): 10000pF
- 2) CAP TOLERANCE: +100/-20%
- 3) DISSIPATION FACTOR: 4% MAX.
- 4) INSULATION RESISTANCE: 25°C 1GOHM
- 5) 100 VDC RATED @ +125°C
- 6) DIELECTRIC WITHSTANDING VOLTAGE: 300 VDC
- 7) CURRENT RATING: 10 AMPS
- 8) REFLOW TEMPERATURE LIMIT: +235°C FOR 5 SEC.
- 9) PACKAGING: BAG (1000 PCS. MAX./ BAG)

MARKING:

PART: NONE
PACKAGE: PART NO.
SCI DATE CODE
QTY.

[illegible]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[API Technologies:](#)

[PSM4F-103Z-10B](#)