


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION

19

© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

REVISIONS					DATE	APPROVED
P	F	ZONE	LTR	DESCRIPTION		
✓	✓	L		REDRAWN & REVISED PER ECN R-1451	9-30-85	REK JLB
✓	✓	M		REV. / ECN R-1546	3-1-86	MAN SLB
✓	✓	N		OBSOLETE - 3 PER R-2760	1-4-87	MAN SLB
✓	✓	P		REV PER ECN DF-5920	11-25-87	SV ABM
✓	✓	R		ADD - 5 PER NPA 0600-4462-9653	10-5-95	ABM
✓	✓	S		REV PER CH14-0241-05	04-05	AA/OE



- 1 REELED FOR USE WITH STANDARD APPLICATORS.
- 2 PLATED WITH .000100 MIN SILVER PER QQ-S-365.
- 3 PLATED WITH .000015 MIN GOLD PER MIL-G-45204 IN THE LOCALIZED GOLD PLATE AREA, GOLD FLASH ON THE REMAINDER, OVER .000030 MIN NICKEL PER QQ-N-290.
- 4 PLATED WITH .000030 MIN GOLD PER MIL-G-45204 IN THE LOCALIZED GOLD PLATE AREA, GOLD FLASH ON THE REMAINDER, OVER .000030 MIN NICKEL PER QQ-N-290.
- 5 PLATED WITH .000050 MIN 93-7% TIN-LEAD ALLOY OVER .000030 MIN NICKEL PER QQ-N-290.
- 6 WIRE RANGE = 10 AWG.
- 7 INSULATION RANGE = .190 - .220 DIA.
- 8 REELED FOR USE WITH QUICK-CHANGE APPLICATOR.
- 9 PLATED WITH .000050 MIN TIN PER ASTM-B-545 OVER .000030 MIN NICKEL PER QQ-N-290.

BLACK	1	66260-5	66254-6	1
BLACK	1	66260-2	66254-5	1
NATURAL	2	66260-4	66254-4	1
BLACK	3	OBSOLETE	66254-3	1
BLACK	4	66260-2	66254-2	1
BLACK	5	66260-1	66254-1	1
TERMINAL LATCH COLOR	FINISH	L.P. ASS'Y P/N REF	STRIP ASS'Y P/N	

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ±.010 ANGLES ±.010	CONTRACT NO DR <i>Rich Rohlbaugh</i> 9-30-85 CHK <i>Larry G. Lawrence</i> 10-25-85 APPD <i>Ed. Black</i> 10-25-85 APPD <i>James E. Smith</i> 10-28-85 DSGN APPD OTHER APPD	NAME MALE TYPE XII GROUND CONTACT STRIP ASSEMBLY SIZE C FSCM NO 00779 DRAWING NO 66254 SCALE NTS SHEET	AMP AMP INCORPORATED Harrisburg, Pa. 17105
MATERIAL SEE CALLOUT	FINISH SEE DASH NO		