

PICCOLO PC D 65 G

Sample photo

Order symbol:	PC D 65 G
Product nbr:	8724307
Description:	Enclosure, PC
Remarks:	Grey cover

EAN:	6418074002112
El. number:	
Finland:	3423409
Denmark:	8212001556
Italy:	7201030
Sweden:	2536814
Norway:	2536509

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		170	80	65	Ingress Protection (EN 60529): IP 66/67
inch:		6.7	3.1	2.6	Impact Resistance (EN 62262): IK 08
Materials:					Electrical insulation: Totally insulated
Material:		Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:		RAL 7035			UV resistance: UL 508
Cover colour:		RAL 7035			Flammability Rating (UL 746 C 5): UL 746C 5V
Cover screws material:		Polyamide			Glow Wire Test (IEC 695-2-1) °C: 960
Cover screws colour:		Grey			NEMA Class: NEMA 1, 4X, 6, 6P, 12, 13
Gasket material:		Polyurethane			Certificates:
Temperatures:					Germanischer Lloyd (GL)
Short term:		-40 ... 120 °C			Underwriters Laboratories
Continuous:		-40 ... 80 °C			Fimko
Short term:		-40 ... 250 °F			Europe EN 62208: 2003
Continuous:		-40 ... 175 °F			UL Canada
Accessories:					Gost R
D-MP		Mounting plate			
DH-3		DIN-35 Mounting rail			
FP 22040		Wall fastening lug (2 pcs)			

PICCOLO 170x80x65-85

