






1 - BLACK PLASTIC HOUSING AND PLUNGER
2 - HOUSING HAS BOSS AROUND PLUNGER TO MEET BSI AND VDE AGENCY
8.0/.315 CLEARANCE REQUIREMENT
3 QUICK CONNECT TERMINALS CONFORM TO 4,78/.188 WIDE X
0.51/.020 THICK NEMA DC-2 SPECIFICATION

CHARACTERISTICS	ELECTRICAL DATA
OPERATING FORCE - - 5,62N/20 OZ APPROX	CONTACT ARRANGEMENT SINGLE POLE
OVERTRAVEL - - - - - 2,00/.079 MIN	16A 1/2HP 125, 250 VAC 3A 125 VAC "L" PILOT DUTY: 150 VA 125, 250 VAC 2A - 24 VDC (CKT 11-12 AND 31-32) 60/75°C (CU) 


THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH. A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

MICRO SWITCH
a Honeywell Division

FED MEG CODE 91939

SWITCH - BASIC

WW1A24A-D8

THIRD ANGLE PROJECTION			
			
SCALE 2:1			
DO NOT SCALE PRINT			
TOLERANCES			
APPLY TO DESIGN UNITS. CONVERSIONS ARE FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE :			
	DIM. mm	TOL mm ±	
NO PLACES	X	1 / .04	X
ONE PLACE	X.X	0.01 / .016	X.X
TWO PLACES	X.XX	0.15 / .006	X.XXX
THREE PLACES			
ANGLES			5° 0.137 / 0
	SI METRIC		US CUSTOMARY
			
WEIGHT			