

1

2


3

4


Cable Kits P/N	10089331-101LF	10089331-102LF	10089331-103LF	10089331-104LF
Lock Screw Length	12.50	12.50	15.00	15.00
AWG	24&26	28&30	24&26	28&30

A


B



C



D




A

B

C

D



spec ref *				dr	Junor Huang	2008-06-03	projection MM	size	A4	scale	1.500		
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	De-Feng Qin	2011-07-19		ecn no	ECR-ELX-DG-005201-2				
				chr	-	-							
				appr	PM ZHENG	2011-07-19					product family		rel level
surface	linear	0.X	±0.3		title	64 pos VDSL			dwg no	10089331		rev	F
		0.XX	±0.15										
		0.XXX	±0.05										
	angular	0°	± 2 °										

ProE File - REV C - 2009-06-09

1

2

3


4

BOM of cable kits 10089331

Component Name	Cable Clamp	Cover TOP	Cover Bottom	Screw lock with cover	Screw Lock with board conn.	Assembled Terminal Block	Shroud
Qt'y/Kit	1	1	1	4	2	2	1

NOTE:

1. This product is not intended to be exposed to a manufacturing solder process.
2. Material:
Diacasting : Zn alloy with cu ,nickel & pure tin plating
Shroud: PBT
Terminal; Copper alloy
Screw: stainless steel
3. Cable O.D:9.7mm-11mm.



spec ref		*		dr	De-Feng Qin	2011-07-19	projection	MM	size	A4	scale	2.000
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	De-Feng Qin	2011-07-19			ecn no			
				chr	PM ZHENG	2011-07-19			rel level			
				appr	Joseph Hsia	2011-07-19			product family		Released	
surface	✓	linear	0.X	±0.3		title	64 pos VDSL Cable connector	dwg no	10089331		rev	F
			0.XX	±0.15								
			0.XXX	±0.05								
	angular	0°	± 2 °	www.fci.com	cat. no.	*	Product - Customer Drw		sheet 2	of 2		

ProE File - REV C - 2009-08-09