




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION, 19
© COPYRIGHT 1983 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS
RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.


REVISIONS					
P	F	ZONE	LTR	DESCRIPTION	DATE
				0 WAS 5085-945	
01	✓			REV. ECN 8578	db 7-20-83
02	✓			REVISED: ECN ABO 501	RDB 10-8-84
03	✓			REV DIM: AB-1594	db 5-86
✓	✓			A REV PER DF-0177 OBS-1520 DF-0777 2P	AS 9-88
✓	✓			B REV. PER ECN DF-1696	N.F. 6-89
✓	✓			C REACTIVATE -2, -5, -11 PER DF-3050	3/93
✓	✓			D REV PER DF-6974 TA	3/93
✓	✓			E REV 0600-5641-96	TT 9-97
				F REV PER ECO-05-0132 89	11-05
				G REV PER ECO-16-004974	KG 12MAY16
					DM



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS $\pm .010$ ANGLES $\pm$		CONTRACT NO DR IRSHAFFNER 5-31-83 CHK 6-2-83 E.A. McDougle APPD 6-2-83 E.A. McDougle APPD 6-2-83 E.T. Parsons		PART NO	
MATERIAL 2 3		DSGN APPD		NAME RECEPTACLE ASSEMBLY, .100 C, 3 ROW WITH MOUNTING EARS, BOX CONTACT, .010 X .020 POST	
FINISH 4		OTHER APPD		SIZE C FSCM NO 00779 DRAWING NO 532786	
				SCALE 5-1 SHEET 1 OF 2	


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION, 19
© COPYRIGHT 1983 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

REVISIONS					DATE	APPROVED
P	F	ZONE	LTR	DESCRIPTION		
			F	SEE SHEET 2		



P.C. BOARD LAYOUT

- 1 AMP, DATE CODE AND PART NUMBER MARKED THIS AREA
- 2 HOUSING MATERIAL: POLYPHENYLENE SULFIDE GST-40F PER MIL-M-24519.
- 3 CONTACT MATERIAL: BERYLLIUM COPPER OR COPPER-NICKEL-SILICONE
- 4 CONTACT FINISH: .000050 GOLD IN CONTACT ENGAGEMENT AREA, TIN-LEAD ON CONTACT TAILS.
- 5 LETTERS INDICATING OUTSIDE ROW AND NUMBERS INDICATING END CAVITIES MARKED THIS SURFACE.
- 6 MIL-C-55302 GROUP "A" INSPECTION REQUIRED.
- 7 LINES INDICATING EVERY FIVE CAVITIES MARKED ON MATING FACE.
- 8 "OBSOLETE PART NUMBER"



.310	6.500	65	6.624	6.725	7.050	7.350	198	1-532786-5
.235	6.400	64	6.524	6.625	6.950	7.250	195	1-532786-4
	4.400	44	4.524	4.625	4.950	5.250	135	1- -3
	3.600	36	3.724	3.825	4.150	4.450	111	1- -2
	1.900	19	2.024	2.125	2.450	2.750	60	1- -1
	4.100	41	4.224	4.325	4.650	4.950	126	1- -0
	4.000	40	4.124	4.225	4.550	4.850	123	-9
	7.900	79	8.024	8.125	8.450	8.750	240	-8
	6.900	69	7.024	7.125	7.450	7.750	210	-7
	5.900	59	6.024	6.125	6.450	6.750	180	-6
	5.400	54	5.524	5.625	5.950	6.250	165	-5
	4.900	49	5.024	5.125	5.450	5.750	150	-4
	3.900	39	4.024	4.125	4.450	4.750	120	-3
	3.400	34	3.524	3.625	3.950	4.250	105	-2
.235	2.900	29	3.024	3.125	3.450	3.750	90	532786-1

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ± .010 ANGLES ±	CONTRACT NO DR IRSHAFFNER 5-31-83 CHK 6-2-83 E.A. McDougle APPD 6-2-83 E.A. McDougle APPD 6-2-83 E.P. Ponsino	AMP AMP INCORPORATED Harrisburg, Pa. 17105
MATERIAL	DSGN APPD	NAME RECEPTACLE ASSEMBLY, .100C, 3 ROW WITH MOUNTING EARS, BOX CONTACT, .010 X .020 POST
FINISH	OTHER APPD	SIZE C FSCM NO 00779 DRAWING NO 532786
		SCALE SHEET 2 OF 2