



Sales Outline Drawing

Revision:

D

Specifications:

| | |
|-----------------------|--|
| Sound Level Category | Medium |
| Mode of Operation | Fast Pulse @ 2 - 10 PPS |
| Voltage Rating | 10 to 48 VAC/DC |
| Frequency | 2900 ± 500 Hz |
| Loudness @ 2 FT | 79 to 89 dB(A) Typ. |
| Loudness @ Min V | 68 dB(A) @ 2 Feet and 10 Vac/dc |
| Loudness @ Max V | 80 dB(A) @ 2 Feet and 48 Vac/dc |
| Current Draw | 6-21 mA |
| Duty Cycle (%) | 50 |
| Housing Material | 6/6 Nylon, Color: Black |
| Storage Temperature | -40° to +85° C |
| Operating Temperature | -30° to +65° C |
| Panel Mounting | Recommended hole size is 1.25"(31.75mm). Thread front will fit standard 30mm(1.181") hole. |
| Knurled Nut | Used to attach part to panel. The max recommended torque is 10 in-lbs. |
| Weight (Typical) | 1.6 oz (45g) |
| NEMA 3R,4X, & 12 | Approved with use of ACC03. |
| Options | Please contact factory. |

Dimensions: Inches (mm)

cUL Recognized

ROHS Compliant

PART DIMENSIONS BEFORE CODE DATE: 1452 5

PART DIMENSIONS AFTER CODE DATE: 1501 1

