

AMPHENOL RF PART NUMBER

000-34000

N-Type Straight Clamp Plug for RG-58, 50 Ohm



PRODUCT IMAGE
COMING SOON

PRODUCT OVERVIEW

RF Connector, N-Type Straight Clamp Plug for RG-58, 50 Ohm

Product Type	Connectors
Product Series	N-Type
Status	Active

PRODUCT SPECIFICATIONS

Gender	Plug
Orientation	Straight
Termination Style	Cable - Clamp
Impedence (Ohms)	50
Body Finish	Nickel
Body Material	Brass
Contact Finish	Silver
Contact Material	Brass
Contact Termination Style	Solder
Insulator Material	PTFE
Cable Group	C
Cable Type	Belden 9907, Belden B7806A, LMR-195, RG-141, RG-303, RG-58, RG-58A, RG-58B, RG-58C
Coupling Mechanism	Threaded
Max Frequency (GHz)	11
Polarity	Standard
Thread Direction	Standard

Min. Temp. (Celsius)	-65
Max. Temp. (Celsius)	165
Mating Cycles	500
Military Qualified	Yes
Military Part Number	UG-536/U

PRODUCT COMPLIANCE

Product compliance documentation, if available is listed below:

RoHS 2 (EU)	Compliant with Exemption 6C
-------------	-----------------------------