




- NOTES:
- 1) 18/2 SVO 90C BLACK WITH 41X34 BARE COPPER STRANDING.
 - 2) CONDUCTOR COLORS: BLACK AND WHITE.
 - 3) 300 VOLTS/10 AMP MAX.
 - 4) APPROVALS: UL & CSA
 - 5) CORDAGE D.D. : .260" (REF.)
 - 6) 100 CORDS/CARTON
 - 7) CORD SET LABEL HAS VOLEX LOGO AND PART NUMBER.
 - 8) PRODUCT IS RoHS & PROP 65 COMPLIANT
 - 9) ALL DIMENSIONS IN INCHES UNLESS OTHERWISE NOTED.

		☒ Indianapolis, IN ☐ Conover, N.C. ☐ Freemont, CA ☐ Aguascalientes, MX ☐ Tijuana, Mexico ☐ Hermosillo, MX ☐ Clinton, AR ☐ Kanata, Canada	
Proprietary Notice:		This document is the property of Volex Incorporated. The information contained herein is not to be disclosed to anyone without the express written consent of Volex Inc.	
MATERIAL:		FINISH: JACKET: SMOOTH	
SCALE: NDT TD SCALE		ECD: N/A	
TOLERANCE UNLESS OTHERWISE SPECIFIED .XXX ± .005 .XX ± .02 .X ± .03 FRACT. ± 1/32° ANGULAR ± 1/2°		ITEM DESCRIPTION 18/2 SVO 12" LG RETRACTILE CORD SET	
APPROVED MAF		DRAWN BY MAF	
PART NO. 6601		DATE: 8/10/07	