



- Durable nylon cable clamps

Part Number:	CCH75-S10-C
Product Family:	Fixed Diameter Cable Clamps
Product Line:	Screw/Rivet Applied
RoHS Compliancy Status:	Compliant
Part Description:	Heavy Duty Fixed Diameter Cable Clamp
Product Type:	Mounting Device
Material:	Nylon 6.6
Color:	Natural
UL Recognized:	E136577
Diameter (In.):	.20
Diameter (mm):	5.1
Width (In.):	.50
Width (mm):	12.7

Bundle Offset (mm):	19.8
Bundle Offset (In.):	.78
Environment:	Indoors
Flammability Rating:	UL94 V-2
Hole Diameter (In.):	.20
Hole Diameter (mm):	5.1
Max. Bundle Diameter (In.):	.75
Max. Bundle Diameter (mm):	19.1
Metric Screw Size:	M5
Mounting Method:	#10 (M5) Screw
Screw Size:	#10 (M5)
Std. Pkg. UOM:	PK
Type Of Application:	Heavy Duty
UOM:	PC
Std. Pkg. Qty.:	100
Min. Order Qty.:	100