



Ty-Rap®

T&B Catalog Number: TY354M
UPC Number: 78621088344
Description: Cable Tie 50lb 14" Natural Nylon with Stainless Steel Locking Device #10 Mounting Hole
Status: Active

General

Material	Nylon 6.6
Color	Natural
Mounting Hole Size	#10

Dimension Information

Length (inches)	14.6
Width (inches)	.184
Max. Wire Bundle Diameter (inches)	4

Specifications

Tensile Strength (lbs.)	50
Temperature Rating	-40°F to 185°F
Flamability Rating	UL 94 V-2

Packaging

T&B Order Multiple	1000
T&B Inner Pack	1000
Package in Units	5000
Package Type	Bulk
T&B Sold in UOM	Each
T&B Weight Per UOM	0.62 lbs. per 100

Application Support

Overview	Available on Website
Material Selection Guide	Available on Website
Available Colors	Available on Website


Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



Cable Ties



Great for use with screws, nuts, and bolts for secure fastening to surfaces.

Ty-Rap® Nylon 6.6 Mounting Head Cable Ties



STD. CAT. NO.	BULK CAT. NO.	BODY WIDTH IN./MM.	LENGTH IN./MM.	MAX. WIRE BUNDLE DIA. IN./MM.	MOUNTING HOLE	TENSILE STRENGTH LBS./N.	STD. PKG. QTY.	BULK PKG. QTY.
TY533M	TY33M	.09/2.29	4.00/101.60	.63/16.00	#4	18/80.07	100	1,000
TY534M	TY34M	.14/3.56	6.00/152.40	1.13/28.70	#8	40/177.90	100	1,000
TY535M	TY35M	.18/4.57	7.80/198.12	1.75/44.45	#10	50/222.40	100	1,000
TY5354M	TY354M	.18/4.57	14.60/370.84	4.00/101.60	#10	50/222.40	100	1,000
—	TY635M	.19/4.83	7.80/198.12	1.77/44.96	.19	50/222.40	—	1,000
TY535M	TYF35M	.19/4.83	7.24/183.90	1.77/44.96	.19	50/222.40	100	1,000
TY537M	TY37M	.30/7.62	13.90/353.06	3.50/88.90	1/4	120/533.80	50	500


For use in temperatures ranging from -40° F to 185° F (-40° C to 85° C).

• Natural nylon color



Ty-Rap® Nylon 6.6 Mounting Head Cable Ties — Weather Resistant

The MX series cable ties are recommended for outdoor use. The addition of carbon black provides good ultraviolet resistance and prolongs the useful life of the cable tie.



STD. CAT. NO.	BULK CAT. NO.	BODY WIDTH IN./MM.	LENGTH IN./MM.	MAX. WIRE BUNDLE DIA. IN./MM.	MOUNTING HOLE	TENSILE STRENGTH LBS./N.	STD. PKG. QTY.	BULK PKG. QTY.
TY533MX	TY33MX	.09/2.29	4.00/101.60	.63/16.00	#4	18/80.07	100	1,000
TY534MX	TY34MX	.14/3.56	6.00/152.40	1.13/28.70	#8	40/177.90	100	1,000
TY535MX	TY35MX	.18/4.57	7.80/198.12	1.75/44.45	#10	50/222.40	100	1,000
TY5354MX	TY354MX	.18/4.57	14.60/370.84	4.00/101.60	#10	50/222.40	100	1,000
TY537MX	TY37MX	.30/7.62	13.90/353.06	3.50/88.90	1/4	120/533.80	50	500

• Black color

For use in temperatures ranging from -40° F to 185° F (-40° C to 85° C).



Ty-Rap® Nylon 6.6 Push Mount Cable Ties

For use in 1/4" and 1/2" pre-drilled holes. Thickness panel .09 max. (TY554M)
Range .04–156 (TY538M)



STD. CAT. NO.	BULK CAT. NO.	BODY WIDTH IN./MM.	LENGTH IN./MM.	MAX. WIRE BUNDLE DIA. IN./MM.	MOUNTING HOLE	TENSILE STRENGTH LBS./N.	STD. PKG. QTY.	BULK PKG. QTY.
TY554M	TY54M	.14/3.56	5.96/151.38	1.13/28.70	1/4	40/177.90	100	1,000
TY538M	TY38M*	.18/4.57	7.80/198.12	1.75/44.45	1/2	50/222.40	100	1,000

*Nylon 6.6 UV weather resistant version available (TY38MX).

For use in temperatures ranging from -40° F to 185° F (-40° C to 85° C).

• Natural nylon color