





LOC	DIST	REVISIONS 変更				DATE	DWN	APVD
J	—	P	LTR	DESCRIPTION				
			F2	REVISED PER ECR-15-006361		23APR15	LP	TD
			F3	REVISED PER ECR-16-015552		3NOV16	DL	T.D



SECT.
断面 A-A



SECT.
断面 B-B



この寸法は 合力によって規定する。
THIS DIMENSION IS CONTROLLED
WITH MATING FORCE
SECT.

断面 C-C

NOTE;

1. THE MATING TAB P/N 170256, 170257
(FOR MULTIPLE Pos.)

- ② REVERSE REEL ④ SEPARATE PAPER TYPE
③ STRESS RELIEVING
FINISH IS SUBJECT TO CHANGE BY THE TYPE OF
STRESS RELIVING PROCESS
INERT GAS FURNACE- - - -MATTE
ATOMOSPHERIC FURNACE FOLLOWED BY ACID PICKLE- - - -BRIGHT SECT.

注記:

1. 嵌合する相手タブは型番170256及び170257で多極用として使用される。
② 逆巻きリール
③ ストレス除去処理
処理法により外観が変わります。
不活性ガス加熱方式 -- 無光沢
大気加熱方式 -- 光沢

② OBSOLETE

—//—		170258-4
TIN PLATING		170258-3
—//—		3-170258-1
TIN PLATING 錫めっき		170258-2
—//—	BRASS THICKNESS 黄銅 板厚0.32	170258-1
FINISH 仕上	MATERIAL 材質	PART NO. 型番

抱合電線切断面積(WIRE RANGE) 2-3. 37 mm ² (AWG#14-12)	被覆外径(INSULATION DIA.) 2.9-3.8 mmΦ
---	--------------------------------------

DIMENSIONS: 単位: 耗 mm TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差 10 以下 : ±0. 2 10を超え30 以下 : ±0. 25 30を超え100 以下 : ±0. 3 角 度 : ±3°	DWN Y.YAMADA 03APR2007	MATERIAL 材料	SEE TABLE	FINISH 仕上	SEE TABLE	③
	CHK MANABA SAKAE 03APR2007	TE Connectivity				
	APVD MANABA SAKAE 03APR2007					
	PRODUCT SPEC 製品規格	NAME 名称	.250 SERIES RECEPTACLE WITHOUT LATCH .250 シリーズ リセプタクル ラッチなし			
	APPLICATION SPEC 取付適用規格	SIZE	CAGE CODE	DRAWING NO 番号	RESTRICTED TO	
	WEIGHT	A4	00779	C= 170258	—	
CUSTOMER DRAWING				SCALE 尺度	1:1	SHEET 1 OF 1
				REV F3		