

You are here: [Products](#) » [Connectors f.con](#) » [PCB connectors](#) » [Female headers](#) » [BL 12 ...](#) » [BL 12 762](#)

► Heatsinks f.cool

► Cases f.case

▼ Connectors f.con

► Sockets

▼ PCB connectors

■ Male headers

■ Female headers

■ Direct female connector

■ Jumpers

► IDC-connectors

► D-Sub connectors

■ Brackets for PC

► Optoelectronics

Female headers

BL 12 762 20 S

for square 0.635 mm, can be put through from above and below

add to request



Features

Technical Drawing

Variants

Accessories / related products

no. of contacts	20
contact material	CuSn alloy
surface contact / contact sleeve	Ni+4...6µm Sn
surface of contact	selective gold-plated
Typ Innenfeder	
plugability	
Einstecktiefe	
plug-in cross-section	square 0.635
insertion / extraction force	
volume resistivity	
capacity between two adjacent contacts	≤ 0,9 pF
nominal current	3 A
nominal voltage	
test voltage	500 V
material isolation body	
temperature range	
class of flammability	UL 94 V-0
insulation resistance	
version	stackthrough
connection type	soldering