



COUPLER, RJ-45
CATEGORY: SEE TABLE, 8 POSITION
HOUSING: THERMOPLASTIC
CONTACTS: PHOSPHOR BRONZE, GOLD OVER NICKEL




SCALE 1:1

PANEL GASKET
ELASTOMER, COLOR: ORANGE




3.5
PANEL NUT
BRASS, NICKEL PLATED


RECEPTACLE HOUSING
POLYESTER, COLOR: BLACK




SCALE 2:1



SCALE 2:1




SUGGESTED PANEL CUTOUT




Ø34.0
PANEL FLANGE

BAYONET LOCK



CAT 6e	NO	1738601-3
CAT 5e	5	1738601-2
CAT 5e	NO	1738601-1
CATEGORY	COUPLER BONDED	PART NUMBER

1. CONNECTOR MAY BE FRONT OR REAR MOUNTED TO A MAXIMUM PANEL THICKNESS OF 3.2 mm.
2. COUPLER LINES CROSSOVER BETWEEN PORTS.
3. THIS PRODUCT HAS NOT COMPLETED VALIDATION TESTING.
4. PANEL NUT AND PANEL GASKET ARE PACKAGED UNASSEMBLED IN POLYBAG.
5. COUPLER BONDED TO HOUSING BY ADHESIVE ALONG EDGE WHERE COUPLER MEETS HOUSING, SEE TABLE.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R.L. KOLLER 25MAR04	 TE Connectivity			
		CHK J. LANDIS 26MAR04				
DIMENSIONS: mm		APVD S. HEADER 17JUN	NAME			
		PRODUCT SPEC 108-2198	RECEPTACLE KIT, INDUSTRIAL CIRCULAR ETHERNET CONNECTOR			
		APPLICATION SPEC 114-13136				
TOLERANCES UNLESS OTHERWISE SPECIFIED:			SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
0 PLC ±0.3 1 PLC ±0.2 2 PLC ±0.10 3 PLC ± 4 PLC ± ANGLES ±°		WEIGHT -	A2	00779	C-1738601	-
MATERIAL -		FINISH -	CUSTOMER DRAWING			
			SCALE	5:2	SHEET	1 OF 1
			REV C1			