


# Ferrules INSULATED (INDUSTRIAL STANDARD)

## French Code <Polypropylene insulated and tin-plated electrolytic copper>



DIN 46228, part 4, except #


| Model No.   | Applicable wire |     | Style | Colour Code | Dimensions (mm) |    |      |      |      |
|-------------|-----------------|-----|-------|-------------|-----------------|----|------|------|------|
|             | mm2             | AWG |       |             | L1              | L2 | D1   | S1   | D2   |
| FWE0.25-6   | 0.25            | 24  | II    | Violet      | 11              | 6  | 0.8  | 0.15 | 1.9  |
| FTR0.5-8    | 0.50            | 20  | II    | White       | 14              | 8  | 1    | 0.15 | 2.6  |
| FTR0.75-8 # | 0.75            | 18  | I     | Light Blue  | 14              | 8  | 1.2  | 0.15 | 3.2  |
| FTR1.0-8 #  | 1.00            | 18  | I     | Red         | 14              | 8  | 1.4  | 0.15 | 3.4  |
| FTR1.5-8 #  | 1.50            | 16  | I     | Black       | 14              | 8  | 1.7  | 0.15 | 3.8  |
| FWE2.5-8    | 2.50            | 14  | I     | Grey        | 14              | 8  | 2.2  | 0.15 | 4.2  |
| FWE4-10     | 4.00            | 12  | I     | Orange      | 17              | 10 | 2.8  | 0.2  | 4.8  |
| FWE6-12     | 6.00            | 10  | I     | Green       | 20              | 12 | 3.5  | 0.2  | 6.3  |
| FWE10-12    | 10.0            | 8   | I     | Brown       | 22              | 12 | 4.5  | 0.2  | 7.6  |
| FWE16-12    | 16.0            | 6   | II    | White       | 24              | 12 | 5.8  | 0.2  | 8.8  |
| FWE25-16    | 25.0            | 4   | I     | Black       | 30              | 16 | 7.3  | 0.2  | 11.2 |
| FWE35-16    | 35.0            | 2   | I     | Red         | 30              | 16 | 8.3  | 0.2  | 12.7 |
| FWE50-20    | 50.0            | 1   | I     | Blue        | 36              | 20 | 10.3 | 0.3  | 15   |

Note: 1) Style I - Suitable for Tri-rated cable, Style II - Standard

2) Maximum operating temperature: + 105°C

3) Delivery lead times may vary depending on the product. These products are **ONLY** available from the following JST affiliates; J.S.T. (U.K.) Ltd, J.S.T. Belgium N.V., J.S.T. India Liaison Office, and JST-SouthAfrica.com.

## German Code <Polypropylene insulated and tin-plated electrolytic copper>



DIN 46228, part 4, except #

| Model No.   | Applicable Wire |     | Style | Colour Code | Dimensions |    |      |      |      |
|-------------|-----------------|-----|-------|-------------|------------|----|------|------|------|
|             | mm2             | AWG |       |             | L1         | L2 | D1   | S1   | D2   |
| GWE0.25-6   | 0.25            | 24  | II    | Light Blue  | 11         | 6  | 0.8  | 0.15 | 1.9  |
| GTR0.5-8    | 0.50            | 20  | II    | Orange      | 14         | 8  | 1    | 0.15 | 2.6  |
| GTR0.75-8 # | 0.75            | 18  | I     | White       | 14         | 8  | 1.2  | 0.15 | 3.2  |
| GTR1.0-8 #  | 1.00            | 18  | I     | Yellow      | 14         | 8  | 1.4  | 0.15 | 3.4  |
| GTR1.5-8 #  | 1.50            | 16  | I     | Red         | 14         | 8  | 1.7  | 0.15 | 3.8  |
| GWE2.5-8    | 2.50            | 14  | I     | Blue        | 14         | 8  | 2.2  | 0.15 | 4.2  |
| GWE4-10     | 4.00            | 12  | I     | Grey        | 17         | 10 | 2.8  | 0.2  | 4.8  |
| GWE6-12     | 6.00            | 10  | I     | Black       | 20         | 12 | 3.5  | 0.2  | 6.3  |
| GWE10-12    | 10.0            | 8   | I     | Ivory       | 22         | 12 | 4.5  | 0.2  | 7.6  |
| GWE16-12    | 16.0            | 6   | II    | Green       | 24         | 12 | 5.8  | 0.2  | 8.8  |
| GWE25-16    | 25.0            | 4   | I     | Brown       | 30         | 16 | 7.3  | 0.2  | 11.2 |
| GWE35-16    | 35.0            | 2   | I     | Beige       | 30         | 16 | 8.3  | 0.2  | 12.7 |
| GWE50-20    | 50.0            | 1   | I     | Olive       | 36         | 20 | 10.3 | 0.3  | 15   |

Note: 1) Style I - Suitable for Tri-rated cable, Style II - Standard

2) Maximum operating temperature: + 105°C

3) Delivery lead times may vary depending on the product. These products are **ONLY** available from the following JST affiliates; J.S.T. (U.K.) Ltd, J.S.T. Belgium N.V., J.S.T. India Liaison Office, and JST-SouthAfrica.com.