


### Description

- In-Line Fuseholders for MINI® Fuses.
- Voltage Rating: 32Vdc maximum
- Current Rating: See Table
- Body material withstands high temps. Protective cover has removable straps.



### Ordering

- Specify packaging and product code



### MINI® Fuse Blade Type Holder

Catalog No.	Description	Fuse Size	Electrical Connection	Maximum Continuous Current Rating
HHL	Black fuseholder w/cover	2-20A	#16 black lead wire; 4" length stripped to 1/4"	16A*
HHL-B	Black fuseholder - Body only			
HHM	Black fuseholder w/cover	2-30A	#12 red lead wire; 4" length stripped to 1/4"	24A*
HHM-B	Black fuseholder - Body only			
HHM-C	Black cover only			

### Bulk Products (Bulk Quantity - 1000 Pieces)

Catalog No.	Description	Fuse Size	Electrical Connection	Maximum Continuous Current Rating
BK/HHL-R	Black fuseholder - Body only	2-20A	#16 red lead wire; 4" length stripped to 1/4"	16A*

\* or 80% of fuse rating, whichever is less

**A fuse must be properly and fully inserted into the holder to provide a solid connection. Poor or improper insertion of the fuse can result in failure of the fuse and holder, thus not protecting the device for which it was intended.**

PACKAGING CODE	
Packaging Code	Description
BK	1,000 pieces in a box

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cooper Bussmann:](#)

[BK/HHM-C](#)