



permanoid



Manufacturers of
Electric Wires, Cables
and Insulating Sleevings,
P.V.C. Compounds

PERMANOID LIMITED

Registered Office:
Hulme Hall Lane
Manchester, M10 8HH, England
Telephone 061-205 6161/7
Telex 667752 Answerback
PERMMR G
Fax 061-205 9325

Branch at Bristol

PERMANOID SPEC. 12/X/124

CONDUCTOR 384/0.05mm tinned annealed copper

INSULATION Silicone rubber to 3.33mm nominal
(Type EI2 150°C rating)

CROSS-SECTIONAL AREA 0.75mm²

TEMPERATURE RANGE For non-flexing applications -100 to +300°C

CURRENT RATING 10 amps (a correction factor must be used
for temperatures above 95°C)

CONDUCTOR RESISTANCE 26.70 ohms/km (max)
