

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [1300250261](#)  
**Status:** **Active**  
**Overview:** [Brad Mini-Change Connectors](#)  
**Description:** Mini-Change Single-Ended Cordset, 5 Poles, Male (Straight) to Female (90°) 16 and 20 AWG, DeviceNet Mid Cable, 5.0m (16.40') Length

**Documents:**  
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**  
CSA LR6837


**General**  
Product Family Industrial Cordsets  
Series [130025](#)  
Connector End A Mini-Change  
Connector End B Mini-Change  
IP Rating IP67  
Material - Contact Brass  
Overview [Brad Mini-Change Connectors](#)  
Product Name DeviceNet Trunk, Mini-Change  
Region Europe  
Type Double Ended  
UPC 78678888469

**Physical**  
Cable Diameter 8.38mm (.330")  
Cable Length 5.0m (16.40')  
Color - Cable Jacket Gray  
Coupling Style Threaded  
Gender Female-Male  
Keyway Single  
LED Indicator No  
Material - Cable Jacket PVC  
Material - Connector Body PVC  
Material - Coupling Nut Die-Cast Zinc  
Material - Plating Mating Gold  
Orientation 90° to Straight  
Poles 5  
Temperature Range - Operating -20°C to +80°C  
Wire Size AWG 16, 20  
Wire/Cable Type Mid Cable

**Electrical**  
Current - Maximum per Contact 4.0A  
Voltage - Maximum 300V AC/DC

**Material Info**  
Engineering Number DNB91A-M050

**Reference - Drawing Numbers**  
Sales Drawing SD-130025-010



Series image - Reference only

|                                                               |                   |
|---------------------------------------------------------------|-------------------|
| <b>EU ELV</b><br><b>Not Reviewed</b>                          |                   |
| <b>EU RoHS</b><br><b>Not Reviewed</b>                         | <b>China RoHS</b> |
| <b>REACH SVHC</b><br>Not Reviewed                             |                   |
| <b>Halogen-Free</b><br><b>Status</b><br><b>Not Reviewed</b>   |                   |
| For more information, please visit <a href="#">Contact US</a> |                   |
| China ROHS                                                    | Not Reviewed      |
| ELV                                                           | Not Reviewed      |
| RoHS Phthalates                                               | Not Reviewed      |

**Search Parts in this Series**  
[130025](#) Series