

24V Combi Drill



Technical Data	
Battery Capacity	1.2Ah
Voltage	24V
Chuck	Keyless
Chuck Size	13mm
No Load Speed	900rpm
Hammer	Yes
Max. Torque	14 N-m
Drilling Capacity∅ :	
Wood	22mm
Steel	10mm
Masonry	13mm

Model: D00016

- Ideal for light trade applications
- 16 torque settings for driving different sizes of screws and drilling various materials
- Suitable for drilling wood, steel and masonry
- Forward and reverse action
- Supplied with 2 x batteries, 1 hour charger, 6 drill bits, 6 screwdriver bits, bit adaptor and blow moulded carry case

435518/520563

Description	Order Code	Price Each
24V Combi Drill	129-3121 ●	
Spare Battery	136-7036	
Spare Charger	136-7037	