




Note:		Not dimensione edges: R 0,5		Scale		5 : 1									
THIS DOCUMENT CONTAINS AAVID THERMALLOY'S INTELLECTUAL PROPERTY WHICH IS SUPPLIED IN CONFIDENCE; IT MUST NOT BE USED FOR ANY PURPOSE OTHER THAN WHICH IT IS SUPPLIED; IT MUST NOT BE REPRODUCED WITHOUT WRITTEN PERMISSION FROM THE OWNERS															
															
 AAVID THERMALLOY EUROPE www.aavidthermalloy.com						A		10May07		ORIGINAL (was ZA4426-9)				RT	
						Format A4		REV		Date		Revision description			
Via XXV Aprile, 32 40057 Cadriano - Bologna ITALY Tel. +39 051 764011 Fax +39 051 764090				Cheney Manor SWINDON WILTS SN2 2QN UK Tel. +44 1793 401400 Fax +44 1793 615396				Die n.		MATERIAL EN10132-4 C67S 42-46 HRC				DRAWING n.  439648	
COMPANY WITH QUALITY SYSTEM CERTIFIED BY LRQA ISO 9001:2000				Factor		GENERAL TOLERANCES		LINEAR ±0,3		Vis. n. 439648		Description: CLIP-STEEL-ZH-W.15.0 SP.0.4 H.19.0-STD ROHS COMPLIANT-(4426G)			
				Perim.		ANGLES ±3°		Drawn R. Tassinari							
				Area		FINISH Zn high resistance plated		Check							
				Weight		RoHS Compliant									
						Corrosion resistance: 50h Neutral salt									