

318 Pocket Digital Thermometer

Test the TPI advantage



Features:

- Field calibrateable to $\pm 2^{\circ}\text{F}$
- Rugged and waterproof (IP63)
- Chisel tip
- Auto off
- Magnetic clip perfect for air duct applications
- 3-year limited warranty



Chisel tip to take surface, air, or immersion temperatures

Specifications:

Temperature Range	-58°F to 300°F (-50°C to 150°C)
Accuracy	$\pm 2^{\circ}\text{F}$ ($\pm 1^{\circ}\text{C}$)
Resolution	0.1°F/°C
Sample Rate	1 reading every 1.5 second
Stem Length	2.8"
Tip Type	Chisel
Water Resistant	Yes
Water Proof	N/A
°C / °F Selectable	Yes
Data Hold	Yes
Auto Off	Yes
Battery Type	LR44

APPLICATIONS:

HVACR

- Ambient Air
- Calibrate

Thermostats

- Vents
- Compressor Heads
- Registers

ELECTRICAL

- Motor Temperatures
- Transformer Temperatures

Chisel



Need chisel tip for surface temperatures. Penetration and/or air tips will not give an accurate surface reading.