




DC Power Jacks




163-5030-E, 163-5031-E

KOBICONN

DC Power Jacks



RECOMMENDED P.C.B. LAYOUT
(COMPONENT SIDE)
P.C.B. THICKNESS=1.60mm



Dimensions: mm

P/N	DIM. A
163-5030-E	2.00±0.1
163-5031-E	2.50±0.1

Material Specifications:

Housing:	High Temp. Plastic
Terminal:	Copper Alloy
Terminal Plating:	Silver on contact and solder all over Nickel
Center Pin:	Copper Alloy
Center Pin Plating:	Nickel

RoHS Compliant

Date Last Revised: 6/29/12

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

KC-301310

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

163-5030-E, 163-5031-E

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[163-5030-E](#) [163-5031-E](#)