





THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE OTHER THAN TYCO ELECTRONICS PERSONNEL WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA, USA.

THIS DRAWING IS UNPUBLISHED.
RELEASED FOR PUBLICATION
COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
U	-	-	-	-	-	-



- NOTES:
- 'UTILUX' OR 'AMP' LOGO STAMPED.
 - THIS PRODUCT IS UL APPROVED.
 - WIRE SIZE RANGE:
CONDUCTOR: 0.5mm² - 1.5mm²
INSULATION: Ø2.3mm - Ø3.2mm



BRASS C26000 PRE-TIN	PRE-TIN	TERMINAL H430ET	1-1627187-3
NICKEL SILVER C75700	NATURAL	TERMINAL H430B	1-1627187-2
BRASS C26000	NATURAL	TERMINAL H430	1-1627187-0
MATERIAL DESC.	FINISH	DESCRIPTION	PART No.
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: W. Riede 09.08.04	tyco Tyco Electronics Corporation Electronics AUSTRALIA
		CHK: H.Thai 09.08.04	
		APVD: WR 09AUG04	
		NAME:	
ALL DIMENSIONS IN mm:	TOLERANCES UNLESS OTHERWISE SPECIFIED: DIMENSION (mm) TOLERANCE(±mm)	PRODUCT SPEC:	TERMINAL, RING/EYE
	LESS THAN 10 0.4	APPLICATION SPEC:	
	OVER 10 TO 30 0.5	WEIGHT: -	
	OVER 30 TO 80 0.7		
	OVER 80 TO 250 1.0		
	ANGLES ±2°		
MATERIAL REF. BLOCK	FINISH REF. BLOCK	SIZE A3	CAGE CODE
		DRAWING NO	RESTRICTED TO
		©- 1627187	-
CUSTOMER DRAWING		SCALE 1:1	SHEET 1 OF 1
			REV 0