




REV.	DATE	DESCRIPTION
NC	03/31/02	INITIAL RELEASE



NOTE:  
1. MAX. PANEL THICKNESS = 6.8mm

8	HEX NUT	BRASS	NICKEL	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS	
7	LOCK WASHER	BRASS	NICKEL	DIMENSIONS IN [ ] ARE IN INCHES FOR CUSTOMER REFERENCE ONLY	
6	GASKET	SILICONE	RED	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .XXX = ± 0.005" .XX = ± 0.010" .X = ± 0.020"	
5	BODY	BRASS	NICKEL	DO NOT SCALE DRAWING	
4	CONTACT PIN	BER. COPPER	GOLD	APPROVALS	
3	INSULATOR	TEFLON	NATURAL	DRAWN	G.R.S.
2	HOUSING	BRASS	NICKEL	CHECKED	
1	DESCRIPTION	MATERIAL	FINISH	DATE	03/31/02
<p style="text-align: center;"><b>Amphenol - Connex</b> CONNECTOR CORPORATION</p> <p style="text-align: center;">TITLE N BULKHEAD JACK TO SMB JACK ADAPTOR</p> <p>SIZE: A    FSCM NO.: 99001    DWG. NO.: 242183.DWG    REV.: NC</p> <p>SCALE: NA    PART NO.: 242183    SHEET: 1 OF 1</p>					