



Terminals

159-3251, 159-7251



Terminals



DIMENSIONS: In.

SPECIFICATIONS	
Maximum Electric Rating:	105°C 300 volts
Terminal Material:	Brass
Thickness:	.032 (0.8mm)
Insulation Material:	Nylon

Mouser Stock No.	Wire Range		Nema Tab (In.)	Insulated Color
	AWG	mm ²		
159-3251	22-16	1.25	.032x.25	Red
159-7251	16-14	2	.032x.25	Blue

Date Last Revised: 8-5-11

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

KC-300023

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

159-3251, 159-7251

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[159-3251](#) [159-7251](#)